



Color: ■ gray

Technical data	
Suitable	for end stops (249-116 and 249-117); for 1 marker or self-adhesive label and transparent protective marker cover
Properties	Snap-on type and adjustable in height from 43.5 mm to 59.5 mm
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0

Physical data	
Width	10 mm / 0.394 inches

Material data	
Color	gray
Weight	1.5 g
Fire load	0.046 MJ

Commercial data	
Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-14-40-75
eCl@ss 9.0	27-14-40-75
ETIM 8.0	EC002248
ETIM 7.0	EC002248
PU (SPU)	50 (25) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332188371
Customs tariff number	39269097900



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 249-119	

Documentation

Bid Text			
249-119	19.02.2019	xml 2.79 KB	
249-119	04.01.2018	doc 24.00 KB	

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 249-119	EPLAN Data Portal 249-119
	WSCAD Universe 249-119
	ZUKEN Portal 249-119

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Label			
Item No.: 210-345 Labels; for laser printer; permanent adhesive; 9.5 x 25 mm; white	Item No.: 210-808 Labels; for Smart Printer; 9.5 x 25 mm; white	Item No.: 210-807 Labels; for Smart Printer; permanent adhesive; 8 x 20 mm; white	Item No.: 210-708 Labels; for TP printers; 9.5 x 25 mm; white

1.1.1.2 Marker

Item No.: 209-113 Cardboard signs; for laser printer; 9.5 x 25 mm; white

1.1.1.3 Protective marker cover




Item No.: 209-114

Protection cover; transparent

Installation Notes

Application



This system can be used as an additional group marker carrier or continuous marking strip carrier for terminal strips or single-deck rail-mount terminal blocks, e.g., for:

- DIN-35 rail-mount terminal strips (264 Series)
- Single-deck rail-mount terminal blocks (279 to 284 Series) with a maximum height of 49 mm (1.93 inch) from upper edge of DIN-rail (observe conductor radius)Receptacles for:
 - 1 x marker
 - 2 x WMB Multi marker or
 - 3 x WCB Combi marker or
 - 1 x WFB continuous marking strip