

MC612PA 1->10 (x10) Horizontal



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems
→ Terminal Block Markers

General Information

Extended Product Type:	MC612PA 1->10 (x10) Horizontal
Product ID:	1SNK150011R0000
EAN:	3472599999466
Catalog Description:	MC612PA Terminal Block Markers pre-printed : 1->10 (x10) Horizontal
Long Description:	MC612PA Terminal Block Markers pre-printed : 1->10 (x10) Horizontal White.

Ordering

Color:	White
Minimum Order Quantity:	1 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160007D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	6 mm
Product Net Height:	12 mm
Product Net Length:	5.6 mm
Product Net Depth / Length:	5.6 mm
Product Net Weight:	11 g

Technical

Spacing:	6 mm
Function:	Pre-printed marker card
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

Technical UL/CSA

Flammability According to UL94:	V2
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225156C1000
---------------------------------	-----------------

Environmental Information:	1SND220060E1000
----------------------------	-----------------

Instructions and Manuals:	1SNK160027C0201
---------------------------	-----------------

RoHS Information:	1SND230504F0204
-------------------	-----------------

Classifications

Object Classification Code:	X
-----------------------------	---

E-number:	2967593
-----------	---------

ETIM 4:	EC000761 - Labelling for terminal block
---------	---

ETIM 5:	EC000761 - Labelling for terminal block
---------	---

ETIM 6:	EC000761 - Labelling for terminal block
---------	---

Container Information

Package Level 1 Units:	1 piece
------------------------	---------

Package Level 1 Width:	120 mm
------------------------	--------

Package Level 1 Depth / Length:	200 mm
---------------------------------	--------

Package Level 1 Gross Weight:	0.011 kg
-------------------------------	----------

Package Level 1 EAN:	3472599999466
----------------------	---------------

Package Level 2 Units:	600 piece
------------------------	-----------

Package Level 2 Gross Weight:	6.6 kg
-------------------------------	--------

Package Level 3 Units:	14400 piece
------------------------	-------------

