



**Part Number :** [192880095](#)

**Product Description :** ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

**Series Number :** 207126

**Status :** Active

**Product Category :** Applicators and Crimp Modules

**Engineering Part Number :** ATP-B-590

---



## Documents and Resources

### Tooling Specifications

[ATS-TOOLING-ID-ATP-001.pdf](#)

[192880095-001.pdf](#)

[TM-640160065-001.pdf](#)

[TM-640160065CN-001.pdf](#)

[TM-640160065DE-001.pdf](#)

[TM-640160065SP-001.pdf](#)

[TM-640160065FR-001.pdf](#)

[TM-640160065IT-001.pdf](#)

[TM-640160065JP-001.pdf](#)

[TM-640160065KR-001.pdf](#)

[TM-640160065MY-001.pdf](#)

[TM-640160065PL-001.pdf](#)

[TM-640160065RU-001.pdf](#)

[TM-640160065SK-001.pdf](#)

[TM-640160065TH-001.pdf](#)

[TM-640160065VN-001.pdf](#)

[TM-640160065TW-001.pdf](#)

[TM-192280498-001.pdf](#)

[TM-192280498SP-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Applicators and Crimp Modules
Series	207126
Description	ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200, 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will

	accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	ETC
Tool Type	Crimp Module
UPC	800753109568
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

## Physical

Net Weight	1.000/g
------------	---------

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Taped Terminal Crimp Module used with TM-3000 and TM-4000 presses with ATP-201 and ATP-301 die sets.	<u>640162000</u>
Use With	Molex ATP-101 style presses

---

### Applicable Parts

Description	Part Number
InsulKrimp Fully Insulated Coupler, Male, for 22-18 AWG Wire, Mylar Tape	<u>190040004</u>
InsulKrimp Fully Insulated Coupler, Male, for 16-14 AWG Wire, Mylar Tape	<u>190040008</u>
InsulKrimp Fully Insulated Coupler, Female, for 22-18 AWG Wire, Mylar Tape	<u>190050004</u>
InsulKrimp Fully Insulated Coupler, Female, for 16-14 AWG Wire, Mylar Tape	<u>190050009</u>
Perma-Seal Male Quick Disconnect Tab for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier	<u>191640016</u>
Perma-Seal Female Quick Disconnect Receptacle for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier	<u>191640018</u>
Perma-Seal Male Quick Disconnect Tab for 16-14 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier	<u>191640049</u>
Perma-Seal Female Quick Disconnect Receptacle for 16-14 AWG Wire, Tab Size 6.35 x	<u>191640051</u>

0.81mm, Mylar Tape Carrier	
----------------------------	--

---

This document was generated on May 19, 2026