



[Printer Labels](#) / [Bradyprinter PR Plus Printer Labels](#) /
3" Core Series UltraTemp Gloss Polyimide Labels

3" Core Series UltraTemp Gloss Polyimide Labels



Product Highlights:

Label/Tape Size:

0.2 in H x 0.65 in W

Material:

Polyimide

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i5100,
BradyPrinter i7100, BRADYPRINTER PR
Plus Series Label Printer, THT 3" Core
Printer

Material Number:

B-727

Color:

White

Quantity per Roll:

10000

Part Number:

THT-14-727-10

ADD TO CART

1



Add To Favorites

Need a different size? Customize it!

PEOPLE ALSO VIEWED

OVERVIEW

High Temperature Polyimide (B-727) withstands wave solder environments and multiple harsh washes for printed circuit board and electronic component preprocess labeling.

- ultra-durable adhesive is designed for use with extreme wash protocol and cleaning chemicals, and is ideal for use in auto apply equipment
- Glossy white polyimide material is thermal transfer printable

- RoHS compliant to 2011/65/EU; UL Approved; Meets requirements of MIL-STD-202C, Method 215K
- Service temperature of -94 to 212° F (-70 to 100° C)

SPECIFICATIONS

Material Number	B-727
Catalog Page #	177
Dimensions	0.2 in H x 0.65 in W
UOM	Roll of 10000 Labels
Finish	Gloss
Label/Tape Size	0.2 in H x 0.65 in W
Maximum Service Temperature °F	572 °F
Meta Description	Brady THT-14-727-10 is a High-Temperature Industrial Polyimide Barcode Label that is 0.200" X 0.650" (5.080 mm X 16.510 mm). Shop online!
Meta Title	BRADY THT-14-727-10 INDUSTRIAL BARCODE LABEL
Minimum Service Temperature °F	-94 °F
Printable Area Dimensions	0.2 in H x 0.65 in W
Printable Area Height	0.2 in
Printable Area Width	0.65 in
Product Number	132474
UPC	754473846459
Quantity per Roll	10000
Quantity per Row	4
Secondary Label Included	Secondary Label is Not Included
Thickness	0.0044 in
Trade Name	UltraTemp®
Unit Price	/Label
Adhesive Type	Acrylic
Applications	Circuit Board ID - After Process, Circuit Board ID - Surface Mount, Circuit Board ID - Through Hole Bottom, Circuit Board ID - Through Hole Top, Component & Equipment ID
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
Label/Media Format	Roll

Label Properties	Heat Resistant Labels, Permanent Adhesive Labels
Material	Polyimide
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant
Shape	Rectangle
Suggested Ribbon Series	R6000

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate

[About](#)

[Careers](#)

[Investors](#)

[Privacy](#)

[Policy](#)

[Terms and](#)

[Conditions](#)

[Terms of](#)

[Use](#)

[ISO](#)

[Certificates](#)

Other BradyContact Sites

[Distributor](#)

[Portal](#)

[International](#)

[Sites](#)

[Safety](#)

[Services &](#)

[Software](#)

[Smart ID](#)

[Brand](#)

[Protection](#)

[Solutions](#)

6555 W.

Good Hope

Rd.

Milwaukee,

WI 53223

Phone: 888-

250-3082

Hours: 7am-

6pm CT

Monday -

Thursday;

Friday 7am-

5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.