

My Parts List

Distributor Inventory Search

Compliance Center

Document Library

Login / Sign Up

Amphenol® RF

Products

Applications

Markets

Resources

Support

Search by part # or keyword

Home

Cable Assemblies

SMA Cable Assemblies

SMA to SMA Cable Assemblies

SMA Straight Plug to SMA Straight Plug LMR-100 50 Ohm 500mm

SMA Straight Plug to SMA Straight Plug LMR-100 50 Ohm 500mm

095-902-589M050

Find In Stock & Buy Now

SMA Straight Plug to SMA Straight Plug LMR-100 50 Ohm 12 inches

+

Add To Parts List

≡

Add To Compare

Product Compliance

• RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)

• California residents see [Prop 65 Warning](#)

• Additional compliance information is available in our [Compliance Center](#).

Description

SMA Straight Plug to SMA Straight Plug LMR-100 50 Ohm 12 inches

Leave a message

Product Life Cycle

Part Status	Active
-------------	--------

Product Specifications

Armor Option	Without Armor
Cable Assembly Type	in-Series
Cable Length	19.69 in (500 mm)
Cable Type	Times LMR-100A
Connector 1 Part Number	901-10604
Connector 2 Part Number	901-10604
Export Control Classification Number	EAR99
Frequency (Max GHz)	6
Impedance (Ohms)	50
Low PIM	No
Mil Qualified	No
Temp (Max Degrees Celsius)	85
Temp (Min Degrees Celsius)	-40

You May Also Be Interested In

Amphenol® RF

SMA Right Angle Plug to SMA Straight Bulkhead Jack RG-142 50 Ohm 36 inches

135111-07-36.00

Amphenol® RF

SMA Straight Jack to SMA Straight Jack RG-174 50 Ohm 36 inches

135108-02-36.00

Amphenol® RF

SMA Right Angle Plug to SMA Right Angle Plug LMR-195 50 Ohm 48 inches

095-902-478-048

Amphenol® RF

SMA Right Angle Plug to SMA Straight Bulkhead Jack LMR-200 50 Ohm 48 inches ARC

095-902-507-048

Amphenol® RF

SMA Straight Bulkhead Jack to SMA Straight Plug RG-174 50 Ohm 500 mm

135110-02-M0.50

Need A Custom RF Cable Assembly?

Build Your Cable Now

Subscribe And Stay Connected With Amphenol RF

Enter EmailAddress

Submit

By submitting your email, you are agreeing to receive occasional updates from Amphenol RF. This site is protected by reCAPTCHA and the Google. [Privacy Policy](#) and [Terms of Service](#) apply.

Company

Quick Links

Support

Account

About Us

Locations

Careers

Newsroom

Capabilities

Quality

Distributor Inventory

Competitor Cross

Reference

Compliance Center

Document Library

Quickbuild RF

Anti-Slavery/Human Trafficking

Contact Us

Local Representative

Locator

Authorized Distributors

Login / Sign Up

My Parts List

Extranet Login

Follow Us

f

🐦

in

▶

Copyright © 2020 Amphenol RF. All Rights Reserved.

Copyright | [Terms & Conditions](#) | [Privacy Policy](#) | [User Agreement](#) | [Logos](#) | [Amphenol.com](#)

Downloaded from [Arrow.com](#)

Contact Us