

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638132300

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for 1.50mm CP Crimp Terminals for CMC Connector

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Taxonomy

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207121

<p style=""margin-top: 0; marginbottom: 0">See Tooling Specification (PDF) Above<p style=""margin-top: 0; marginbottom: 0">Extraction Tool for removal of 98915 Series

Extraction

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Crimp Presses and Crimp Hand T

Extraction Hand Tool

800756711881

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight


4.950/zg

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638132300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
1.50mm CMC CP Female Terminal, Tin Plated, for Tab Ddimensions 1.50mm x 0.80mm, Wire Size 0.50mm² - 1.0mm²	643231029
1.50mm CMC CP Female Terminal, Tin plated, for Tab Dimensions 1.50mm x 0.80mm, Wire Size > 1.0mm²- 2.0mm²	643231039
1.50mm CMC CP Female Terminal, Tin plated; Selective 1.27µm Gold in Contact Area, for Tab Dimensions 1.5mm x 0.8mm, Wire Size > 1.0mm² -2.0mm²	643231219

1.50mm CMC CP 643231319
Female Terminal,
Tin plated; Selective
1.27µm Gold in
Contact Area, for
Tab Dimensions
1.5mm x 0.8mm,
Wire Size 0.5mm²
-1.0mm²

This document was generated on 08/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION