

# ZBF 5,QR:FORTL.ZAHLEN 41-50 - Zack marker strip



0808697:0041

<https://www.phoenixcontact.com/us/products/0808697:0041>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Zack marker strip flat, 10-section, vertically labeled with the consecutive numbers: 41 ... 50, white, for terminal block width: 5 mm, mounting type: snapped



## Commercial data

Item number	0808697:0041
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918596286
Weight per piece (including packing)	0.568 g
Weight per piece (excluding packing)	0.568 g
Customs tariff number	49119900
Country of origin	DE

# ZBF 5,QR:FORTL.ZAHLEN 41-50 - Zack marker strip



0808697:0041

<https://www.phoenixcontact.com/us/products/0808697:0041>

## Technical data

### Product properties

Product type	Labeled terminal marker
Pitch	5 mm
Type	flat

### Marking

Printing	41 ... 50
----------	-----------

### Mounting

Mounting type	snapped
---------------	---------

### Material specifications

Color	white
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Dimensions

Text field width	5.15 mm
Text field height	5.15 mm
Pitch	5 mm

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# ZBF 5,QR:FORTL.ZAHLEN 41-50 - Zack marker strip



0808697:0041

<https://www.phoenixcontact.com/us/products/0808697:0041>

## Classifications

### ECLASS

ECLASS-11.0	27281101
ECLASS-12.0	27281101
ECLASS-13.0	27281101

### ETIM

ETIM 9.0	EC000761
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)