Specifications





Eaton 170M4016

Eaton Bussmann series high speed square body fuse, 690V (IEC), 630A, 200 kAIC, Top fuse status indicator, Fuse, Blade end X blade end, Class aR, DIN 43 620

General specifications

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4016
MODEL CODE	FUSE 630A 690V 1/80 AR UC INDICATOR
UPC	051712257480
EAN	5027590450935
PRODUCT LENGTH/DEPTH	245 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	459 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized
GLOBAL CATALOG	170M4016
PRODUCT TYPE	High speed square body fuse

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

AMPERAGE RATING	630 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	350000 at 660 V
WATT LOSSES	80 W
CLEARING LOSS	80
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	52000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 /80 Visual indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

Resources

CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf 170M4016~Eaton Bussmann series high speed square body fuse Bussmann series complete full line catalog no. 1007
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250910en.pdf eaton-high-speed-square-body-fuse-declaration-of-conformity-eu250032en.pdf
DRAWINGS	eaton-fuses-fuse-link-dimensions-002.eps
MANUALS AND USER GUIDES	High speed fuses application guide
MCAD MODEL	eaton-hs-sq-body-fuses-mcad-drawings-550-690v-1-80.dwg eaton-hs-sq-body-fuses-mcad-3d-models-550-690v-1-80.stp
PEP ECO-PASSPORT	eaton-hs-square-body-fuses-pep-eato-00447-v0101-en.pdf
PRODUCT NOTIFICATIONS	eaton-bussmann-series-170m-fuses-product-change-notice-pcn-bur-00193-en-us.pdf eaton-bussmann-series-ukca-marking-high-speed-fuses-pcn-bur-00167-en-gb.pdf
TECHNICAL DATA SHEETS	720014 DIN 43653 690V

Downloaded from Arrow.com.

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.