



**TECHFLEX**  
Braided Sleeving Products




PRODUCTS

ONLINE DEALERS

LOGIN



Home > General Purpose > Flexo F6®



## Flexo F6®

F6N0.50BK - F6 - Self-Wrapping Braided Sleeving - 1/2" - Black

Choose a size:


(\*) denotes product is not available in the color that is currently selected

[Change units to Metric](#)

Choose a color:



## Flexo F6®



F6's unique split, semi-rigid braided construction makes it the ideal solution for situations where ease of installation is of primary importance.


The lateral split allows the tube to open up to accommodate a wide variety of bundling requirements, and the semi-rigid braid configuration simply closes around the entire installation without the need for any additional fasteners (velcro, tape, etc.)

The 10 mil PET braid is lightweight, quiet and flexible. The 25% edge overlap (at nominal diameter) allows it to fit around inline plugs, connectors and splices.

F6 will bend to a tight radius, will not pinch wires, can be easily cut to size and, unlike full rigid tubing, will not impede the removal or removal of wires.

As easy as installing cables quickly and





**EVERYTHING**

**BE THE FIRST IN THE KNOW**

We're constantly developing new products to meet the needs of our customers in a wide variety of industries. Sign up to receive exciting news about our latest innovations and to learn what we're up to.

## Certifications:



## Product Sizes


Size	Part Number	Wall Thickness Max	Bulk Spool	Box A	Box B	Lbs / 100'
1/8"	F6N0.13	.024"	8,000'	400'	100'	0.470
1/4"	F6N0.25	.025"	3,000'	200'	100'	0.600
3/8"	F6N0.38	.025"	1,500'	150'	75'	1.200
1/2"	F6N0.50	.025"	1,200'	150'	75'	1.400
3/4"	F6N0.75	.025"	500'	100'	50'	1.600
1"	F6N1.00	.038"	400'	100'	50'	2.000
1 1/4"	F6N1.25	.038"	250'	75'	25'	2.400
1 1/2"	F6N1.50	.038"	250'	75'	25'	2.700
2"	F6N2.00	.038"	200'	50'	25'	3.600

[Change units to Metric](#)

## Additional Information



F6 / F6 Quiet



F6 Installation Tool



Please [Log In](#) For Additional Information

## RESOURCES

- Product Guides
- Data Sheets
- Archived Documents
- Tips & Techniques
- Sleeving Selector
- Glossary
- Conversion Tables
- Solutions Matter

## ABOUT US

- Heritage
- Sponsorships
- Trademarks
- Policies
- Affiliations
- News
- Careers
- Projects

## TF CUSTOM

- Heatshrink Printing
- Custom Printing
- Precision Cutting
- Engineered Materials
- Specialty Packaging
- Packaged Kits
- Braid Shaping

## CONTACT US

🌐 104 Demarest Road  
Sparta, NJ 07871  
🕒 9:00am - 5:30pm EST  
☎ 878-888-8848

Our website uses cookies to improve your experience and record usage statistics. By using Techflex.com you consent to cookies as described in our Terms and Conditions.

[Learn More](#)

OK

🌐 English | 日本語 | Español

© 2025 Techflex, Inc. All Rights Reserved. | [Terms of Use](#) | [Sitemap](#) | [Contact Us](#)