



AT06-3S-MM01BLK 3-WAY PLUG, BLACK FEMALE CONNECTOR WITH REDUCED DIAMETER SEAL (E-SEAL) AND END CAP. COMPATIBLE TO PART # DT06-3S-CE01

PART NUMBER: AT06-3S-MM01BLK

DATASHEET: View / Download

SPECIFICATIONS:

AMP: 13
AWG: 10-14
Color: Black
Contact Size: 12
Contact type (Pin/Socket): Socket
Dielectric Value: 1500V minimum
Housing Material: Thermoplastic
Insulation Resistance: 1000 megohms at 25°C
IP Rating: IP67
Mating Cycle Durability: >100
No. of Positions: 2-Way
Operating Temperatur: -55°C to +125°C
Seal Diameter: .053" - .120"
Seal Material: Silicone Elastomer
Seal Wire Range (mm): 2.46 - 4.01
Mating Part(s): AT04-3P* Receptacle
Wedgelock Part Number: AW3S
Wire Range: 14-20 AWG

QUANTITY

1 REQUEST A QUOTE

Like Sign Up to see what your friends like.
Like Sign Up to see what your friends like.

Downloaded from Arrow.com.

3-Way Plug, Black Female Connector with Reduced Diameter Seal (E-Seal) and End Cap. Compatible with DT06-3S-CE01.

RELATED ITEMS



AT04-3P-BLK 3-Way Receptacle, Male, Black. Compatible to part # DT04-3P-E004



AW3S 3-Way Wedgelock Plug, Compatible to part # W3S



A Series Thermoplastic Connectors Catalog



AT04-3P-EC01BLK 3-Way Receptacle, Male, End Cap, Black. Compatible to part # DT04-3P-E005



AT04-3P-MM01BLK 3-Way Receptacle, Male, Reduced Diameter Seal (E-Seal), End Cap, Black. Compatible to part # DT04-3P-CE03



AT04-3P-PM05- Flange Mount Receptacle with Gasket



AT04-3P-RD01BLK 3-Way Receptacle, Male, Reduced Diameter Seal (E-Seal), Black. Compatible to part # DT04-3P-CE02



AT04-3P-RY01 3-Way Receptacle, Male, "Y" Connector (J1939). Compatible to part # DT04-3P-P007



AT04-3P-SR01BLK 3-Way Receptacle Male Connector with Strain Relief, Endcap and Standard Seal



AT04-3P-SR02BLK - 3-Way Receptacle Male Connector with Strain Relief and Endcap, Reduced Seal



AT06-3S-BLK, 3-Way Plug, Female, Black. Compatible to part # DT06-3S-E004



AT06-3S-EC01BLK, 3-Way Plug, Female, End Cap, Black. Compatible to part # DT06-3S-E005

Downloaded from Arrow.com.



AT06-3S-RD01BLK, 3-Way Plug, Female, Reduced Diameter Seal (E-Seal), Black. Compatible to part # DT06-3S-CE02



AT06-3S-RJ120BK, 3-Way, Plug, J1939-11, 120 Ohm Resistor, Gold Sockets, Blue Wedgelock, Black. Compatible to part # DT06-3S-EP10



AT06-3S-SR01BLK, 3-Way Plug Female Connector with Strain Relief and Endcap, Standard Seal



AT06-3S-SR02BLK, 3-Way Plug Female Connector with Stain Relief and and Endcap, Reduced Seal



AT04-3P 3-Way Receptacle, Male. Compatible to part # DT04-3P



AT04-3P-EC01 3-Way Receptacle, Male, End Cap. Compatible to part # DT04-3P-E003



AT04-3P-KIT01 3-Way Pin Receptacle, Wedge and Contacts Kit



AT04-3P-MM01 3-Way Receptacle, Male, Reduced Diameter Seal (E-Seal), End Cap. Compatible to part # DT04-3P-CE01



AT04-3P-RD01 3-Way Receptacle, Male, Reduced Diameter Seal (E-Seal). Compatible to part # DT04-3P-C015



AT04-3P-RJ120 3-Way, Receptacle, J1939-11, 120 Ohm Resistor, Gold Pins, Blue Wedgelock, Gray. Compatible to part # DT04-3P-P006



AT04-3P-RJ120BK 3-Way, Receptacle, J1939-11,120 Ohm Resistor, Gold Pins, Blue Wedgelock, Black. Compatible to part # DT04-3P-EP10



AT04-3P-SS01 3-Way Receptacle, Male Connector with Solid Rear Grommet and Endcap. Compatible to part # DT04-3P-C017









Downloaded from Arrow.com.

AT06-3S, 3-Way Plug, Female. Compatible to part # DT06-3S

AT06-3S-KIT01 3-Way Socket Plug, Wedge and Contacts Kit

AT06-3S-MM01, 3-Way Plug, Female, Reduced Diameter Seal (E-Seal), End Cap. Compatible to part # DT06-3S-CE01

AT06-3S-R680 3-Way Plug, 680 Ohm Resistor, End Cap, Grey









AT06-3S-RD01, 3-Way Plug, Female, Reduced Diameter Seal (E-Seal). Compatible to part # DT06-3S-C015

AT06-3S-RJ120, 3-Way Plug, Female, 120 OHM Terminating Resistor (J1939). Compatible to part # DT06-3S-P006

A114017 - Seal Plugs, White

AT06-3S-CAP Protective Cover for 3-way Plug









ATRT-100 - Contact Removal Tool

65-54756 - Diagnostic Grade Gold-Plated Male Contact Pin

AT60-14-0122 - Stamped & Formed Nickel-Plated Male Contact, Size 16

AT60-14-0144 - Stamped & Formed Gold-Plated Male Contact, Size 16









AT60-16-0122 - Stamped & Formed Nickel-Plated Male Contact, Size 16

AT60-16-0144 - Stamped & Formed Gold-Plated Male Contact, Size 16

AT60-16-0622 - Stamped & Formed Nickel-Plated Male Contact, Size 16

AT60-16-0644 - Stamped & Formed Gold-Plated Male Contact, Size 16

Downloaded from Arrow.com.



AT60-202-16141 - Solid Machined Nickel-Plated Male Contact, Size 16



AT60-202-1631 - Solid Machined Gold-Plated Male Contact, Size 16



AT60-215-1631 - Solid Machined Gold-Plated Male Contact, Size 16



AT62-14-0122 - Stamped & Formed Nickel-Plated Female Contact, Size 16



AT62-14-0144 - Stamped & Formed Gold-Plated Female Contact, Size16



AT62-16-0122 - Stamped & Formed Nickel-Plated Female Contact, Size 16



AT62-16-0144 - Stamped & Formed Gold-Plated Female Contact, Size 16



AT62-16-0622 - Stamped & Formed Nickel-Plated Female Contact, Size 16



AT62-16-0644 - Stamped & Formed Gold-Plated Female Contact, Size 16



AT62-201-16141 - Solid Machined Nickel-Plated Female Contact, Size 16



AT62-201-1631 - Solid Machined Gold-Plated Female Contact, Size 16



AT62-209-16141 - Solid Machined Nickel-Plated Female Contact, Size 16



AT62-209-1631 - Solid Machined Gold-Plated Female Contact. Size 16



AT-RK100 - Large Field Repair Kit



ATT-16-00 - Size 16 Stamped and Formed Contact Tool 14-16 AWG



ATT-16-01 - Size 16 Stamped and Formed Contact Tool 18-20 AWG

Downloaded from Arrow.com.



CA-5D12 - Universal Hand Crimp Tool, Size 12/16/20 Solid Contacts Only



CA-5E12 - Pneumatic Crimp Tool, Size 12/16/20 Solid Contacts Only



MFX-3950 - Size 16 Crimp Die for Stamped and Formed Contacts 18-20 AWG



MFX-3953 - Size 16 Crimp Die for Stamped and Formed Contacts 16-18 AWG



MFX-3975 - Size 16 Crimp Die for Stamped and Formed Contacts 14-16 AWG

BROWSE SIMILAR ITEMS

- Our Product Lines > A Series > AT Series > 3-Way Plugs
- Market Applications > Heavy Equipment > Construction > A Series > AT Series > 3-Way Plugs
- Market Applications > Heavy Equipment > Transportation > A Series > AT Series > 3-Way Plugs
- Market Applications > Heavy Equipment > Off Road Recreation > A Series > AT Series > 3-Way Plugs
- Market Applications > Automotive > Diagnostics > A Series > AT Series > 3-Way Plugs
- Market Applications > Water Resistant - Waterproof > A Series > AT Series > 3-Way Plugs
- Market Applications > Harsh Environments > A Series > AT Series > 3-Way Plugs

Downloaded from Arrow.com.

Copyright 20182018 Amphenol Sine Systems. All Rights Reserved. eCommerce Software by 3dcart.

Downloaded from Arrow.com.