

Part Number : [503978001](#)


Product Description : CP-3.3 Wire-to-Board Crimp Terminal, Female, 24-22 AWG, Reel

Series Number : 50397

Status : Active

Product Category : Crimp Terminals

Packaging Alternative : [503978101](#) (Bag)



Documents and Resources

Drawings

[503978001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[SPK-50397-001-001.pdf](#)

[2122090000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	50397
Description	CP-3.3 Wire-to-Board Crimp Terminal, Female, 24-22 AWG, Reel
Application	Power, Wire-to-Board
Product Name	CP-3.3
UPC	193264100101

Electrical

Current - Maximum per Contact	8.5A
Voltage - Maximum	500V AC/DC

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	103.000/mg
Packaging Type	Reel
Plating min - Mating	0.914µm

Plating min - Termination	0.914µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-1.80mm
Wire Size (AWG)	22, 24
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
CP-3.3 Dual Row Receptacle Housings	<u>212209</u>

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for CP-3.3 Receptacle Terminals, 24-22 AWG, UL1007 Wire	<u>2130693800</u>
FA2 Pneumatic Feed Crimp Applicator for CP-3.3 Receptacle Terminals, 24-22 AWG	<u>2130693810</u>
Hand Crimp Tool for CP-3.3 Receptacle Crimp Terminals, 28-22 AWG, UL1007 Wire	<u>2133095100</u>

Japan

Description	Part Number
S-1 Applicator for CP-3.3 Crimp Terminals, 24-22 AWG	<u>573163710</u>

This document was generated on Apr 30, 2026