

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see our [Privacy Statement](#).

Don't show this message again

Choose Language  English

**Honeywell** | Sensing and Control

Search the entire website and product database


Start Here ...

Search

HOME ABOUT US KEY INDUSTRIES SERVED PRODUCTS & INFORMATION NEWS & EVENTS SALES & SUPPORT LOGIN

## 91SX51

( [Home](#) : [Products](#) : [Switches](#) : [MCR0 SWITCH™ Basic Switches](#) : [Premium Miniature and Subminiature Switches](#) : [SX Switches](#) )



SX Series Subminiature Basic Switch, Single Pole Double Throw (SPDT), 28 Vdc, 7 A, Pin Plunger Actuator, Solder Termination

Actual product appearance may vary.

Sales & Service

Distributor Inventory

Overview

Specs

Documentation

Application Notes

### Product Specifications

Switch Type	MCR0 SWITCH™ Subminiature 8,89 mmHx 5,08 mmW x 12,7 mmL [0.35 in H x 0.20 in W x 0.5 in L]
Sealed	No
Ampere Rating	7 A
Circuitry	SPDT
Actuator	Pin Plunger
Termination	Solder
Operating Temperature	-53 °C to 85 °C [-65 °F to 185 °F]
Voltage	28 Vdc
Contact Type	Silver
Operating Force (OF)	1,39 N [5.0 oz] max.
Release Force	0,28 N [1.0 oz] min.
Pretravel (PT)	0,5 mm [0.020 in] max.
Overtravel (OT)	0,1 mm [0.004 in] min.
Differential Travel (DT)	0,12 mm [0.005 in] max.
Operating Position (OP)	8,13 mm ± 0,38 mm [0.320 in ± 0.015 in]
Housing Material	General Purpose Phenolic/Valox 420
Mounting Screw Size	22,1 mm [0.087 in]
Mounting Centers	4,83 mm [0.19 in]
Tightening Torque	0,22 N m [2.0 in lb]
Weight	1,36 g [0.003 lb]
Package Height	8,89 mm [0.35 in]
Package Width	5,08 mm [0.20 in]
Package Length	12,7 mm [0.50 in]
Recommended For	Most applications
Comment	Printed Circuit Board Terminals plated for soldering
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	SX Switches

Distributor Inventory

Input part number for stock availability

## Narrow Your Search

### Modify Your Search

#### Products

Select Option

#### Technology

Select Option

#### Industries Served

Select Option

Product Search

Product Type:    
Industry:    
Search Term:

New Products Only  
 Entire Product Catalog

### My Links

- › eCOM Login
- › Request Access to eCOM
- › Rep/AD Portal Login
- › Rep/AD Portal Access Request
- › Sample Request
- › Digital U - HML Learning Hub Login
- › Digital U - HML Learning Hub Access Request
- › Limitless Microsite
- › Supplier Microsite

### Literature and Media

- › Data Sheets
- › Videos
- › Literature
- › Literature Request
- › White Papers
- › Application Notes
- › Application Demos
- › CAD Renderings

### Contacts

- › Customer Service
- › Technical Support
- › Global Sales & Service
- › Website Feedback

