



Part Number : [2130690100](#)

Product Description : FA2 Mechanical Feed Crimp Applicator for Micro-Lock Plus Terminals, 26-22 AWG, UL1061 and 0.30mm² AVSS Wire

Series Number : 207127

Status : Active

Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

[2130690100-000.pdf](#)

[TM-638000029-001.pdf](#)

[638080200-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FA2 Mechanical Feed Crimp Applicator for Micro-Lock Plus Terminals, 26-22 AWG, UL1061 and 0.30mm ² AVSS Wire
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FA2, Micro-Lock Plus
Tool Type	Applicator
UPC	193264136216
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Micro-Lock Plus Female Crimp Terminal, 2.00mm Pitch, Matte Tin (Sn) Plating, 26-22 AWG, Reel	<u>5055721000</u>
Micro-Lock Plus Female Crimp Terminal, 2.00mm Pitch, 0.10µm Gold (Au) Plating, 26-22 AWG, Reel	<u>5055721100</u>
Micro-Lock Plus Female Crimp Terminal, 2.00mm Pitch, 0.38µm Gold (Au) Plating, 26-22 AWG, Reel	<u>5055721200</u>
Micro-Lock Plus Female Crimp Terminal, 2.00mm Pitch, 0.76µm Gold (Au) Plating, 26-22 AWG, Reel	<u>5055721300</u>

This document was generated on Jan 04, 2026