



P	LTR	DESCRIPTION	DATE	DWN	APVD
	T1	PART STATUS CHANGE TO DISCONTINUANCE	07AUG2026	ABS	PS



DIM B REF
— CUSTOMER
PC BOARD
THICKNESS



SECTION J-J



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 150CT2001		TE Connectivity			
		CHK J OLSON 120CT01					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT, RCPT, MOD II, STRIP, SHORT POINT OF CONTACT, HORIZONTAL, TYPE 'C' ENTRY —			
		APVD J OLSON 120CT01					
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		PRODUCT SPEC — APPLICATION SPEC —					
MATERIAL —		FINISH — WEIGHT —					
CUSTOMER DRAWING				SIZE A2	CAGE CODE 00779	DRAWING NO C=85863	RESTRICTED TO —
SCALE 10:1						SHEET 1 OF 2	REV T1

4

3

2

1

© -TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B

A

1

CONTACT LEGS SHOWN IN PHANTOM AND SHEAR LINES DEFINE LOOSE PIECE PART.

2

.000030 GOLD OVER .000050 NICKEL.

3

.000050 GOLD OVER .000050 NICKEL.

4

GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000030 GOLD IN CONTACT AREA ONLY.

5

GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD IN CONTACT AREA ONLY.

6

TIN PLATE.

7

POINT OF MEASUREMENT FOR PLATING THICKNESS(INSIDE OF CONTACT BEAMS).

8

NOTE DELETED

9

OBSOLETE.

9	.093	.145	2-85866-1	5	2-85863-1
9	.062	.115	1-85866-2	3	1-85863-2
9	.062	.115	1-85866-1	5	1-85863-1
9	.125	.175	1-85866-0	4	1-85863-0
9	.125	.175	85866-9	6	85863-9
9	.125	.175	85866-8	2	85863-8
9	.093	.145	85866-7	4	85863-7
9	.093	.145	85866-6	6	85863-6
9	.093	.145	85866-5	2	85863-5
9	.062	.115	85866-4	4	85863-4
9	.062	.115	85866-3	6	85863-3
	.062	.115	85866-2	2	85863-2
DIM B		DIM A	LOOSE PIECE PART NUMBER	FINISH	STRIP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

FINISH
-

DWN
R BROWN
15OCT01

CHK
J OLSON
12OCT01

APVD
J OLSON
12OCT01

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

TE Connectivity

CONTACT, RCPT, MOD II, STRIP, SHORT
POINT OF CONTACT, HORIZONTAL, TYPE 'C' ENTRY

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-85863

RESTRICTED TO
-

SCALE
1:1

SHEET
2 OF 2

REV
T1

1471-9 (1/15)

Downloaded from Arrow.com