



Commercial status

This Product is Obsolete : JUN 14, 2022

⚠ This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
PDU Type	Metered
Cable length	10 Ft (3.05 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets Toolless Mounting Kit

Complementary

Main Input Voltage	200 V 208 V 230 V
Height	49.02 In (124.5 cm)
Width	2.20 In (5.6 cm)
Output voltage	230 V
Depth	1.73 In (4.4 cm)
Net Weight	6.77 Lb(US) (3.07 kg)
Mounting Location	Side
Mounting preference	No preference
Input Connection Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Number of rack unit	0U
Mounting position	Vertical
Acceptable Input Voltage	200...250 V
Max line current	10 A
Load Capacity	2300 VA

Input Frequency	47...63 Hz
Number of power socket outlets	16 IEC 60320 C13

Environment

Product Certifications	CE[RETURN]GOST[RETURN]VDE
Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 Ft (0...15240 m)

Ordering and shipping details

GTIN	731304220886
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	84.02 In (213.4 cm)
Package 1 Width	15.24 In (38.7 cm)
Package 1 Length	12.72 In (32.3 cm)
Package weight(Lbs)	8.757 Lb(US) (3.972 kg)

Environmental data

Lead free	Yes
Mercury free	Yes
Sustainable packaging	No
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
EU RoHS Directive	Compliant with Exemptions  EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Circularity Profile	 End Of Life Information
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **End of commerc. - Block**

AP7850 may be replaced by any of the following products:



AP7850B

APC NetShelter Metered Rack PDU, 0U, 10A, 230V, 16 C13 outlet

Qty 1

Substitution date: |