

## Fuse plug - ST-SILED 12-UK 4 - 0921024

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, Nominal current: 6.3 A, Length: 33.1 mm, Width: 6.1 mm, Height: 45.7 mm, Color: black

The illustration shows the version without LED/light indicator

RoHS

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 010287
GTIN	4017918010287
Weight per Piece (excluding packing)	5.880 g
Custom tariff number	85369095
Country of origin	Poland

### Technical data

#### General

Note	If the fuse is defective, the downstream circuit is not off load
Color	black
Insulating material	PA
Flammability rating according to UL 94	V2

#### Dimensions

Width	6.1 mm
Length	33.1 mm

#### General

Fuse	G / 5 x 20
------	------------

# Fuse plug - ST-SILED 12-UK 4 - 0921024

## Technical data

### General

Insulating material group	CTI 600
Maximum load current	6.3 A
Nominal current $I_N$	6.3 A
Nominal voltage $U_N$	250 V

### Connection data

Connection method	Plug connection
-------------------	-----------------

### Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	V2

## Approvals


### Approvals


#### Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals


### Approval details


CSA		<a href="http://www.csagroup.org/services/testing-and-certification/certified-product-listing/">http://www.csagroup.org/services/testing-and-certification/certified-product-listing/</a>	13631
Nominal current $I_N$	10 A		
Nominal voltage $U_N$	300 V		

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 60425
Nominal current $I_N$	6.3 A		
Nominal voltage $U_N$	300 V		

## Fuse plug - ST-SILED 12-UK 4 - 0921024

### Approvals

cUL Recognized			<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 60425
Nominal current I <sub>N</sub>		6.3 A		
Nominal voltage U <sub>N</sub>		300 V		

EAC		EAC-Zulassung
-----	---	---------------

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
------------------	---	---