

Specification Sheet

Part Number: 151-00513



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval features and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Conn. Clip w/Oval Arrowhead, 0.6-1.0mm Panel Thick, 6.2x12.2 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Article Number

151-00513

Type

YCCSFT62122

Color

Black (BK)

Quantity Per

bag

Product Description

Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description

Conn. Clip w/Oval Arrowhead, 0.6-1.0mm Panel Thick, 6.2x12.2 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Global Part Name	YCCSFT62122-PA66HIRHS-BK
Length L (Metric)	27.5
Fixation Method	Arrowhead for oval holes
Width W (Metric)	16.0
Height H (Metric)	14.1
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.04
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	1.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.48
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Max (Metric)	12.2
Disc Diameter (Metric)	22.0
Disc Diameter (Imperial)	0.87
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).