Part Number : 431781001
Product Description : Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact
Series Number : 43178
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

431781001_sd.pdf

431780000-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PSX-43335-9999-001.pdf

PS-44441-9999-001.pdf

444410000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	43178
Description	Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact
Product Name	Sabre
UPC	800754378314

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Unplated
Material - Plating Termination	Unplated
Net Weight	0.565/g
Packaging Type	Reel

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.30mm max.
Wire Size (AWG)	18
Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sabre Female Crimp Terminals	43375

Use with Part(s)

Description	Part Number
Sabre Plug Crimp Housings	43680

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Sabre Terminals, 18-14 AWG	638117200
Manual Extraction Tool	638130800
Mini-Mac Applicator	638919000

Downloaded from Arrow.com.