



4-1971773-3 Product Details

 Share  Print  Email



 Active

 View 3D PDF

Power Triple Lock Connector System

1x3 plug housing Key D yel

4-1971773-3 

TE Internal Number: 4-1971773-3

Product Highlights [View All](#)

- Power Triple Lock Product Line
- Wire-to-Wire
- Applies To Wire/Cable
- Connector
- Connector Assembly

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through
Distributor 

 Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Line	Power Triple Lock
Product Type	Connector
Connector Type	Connector Assembly

Mechanical Attachment

Mating Retention Type	Latch(ing)
-----------------------	------------

Electrical Characteristics

Operating Voltage (VAC)	600
Operating Voltage (VDC)	600

Body Features

Mating Retention	With
------------------	------

Contact Features

Contact Layout	In-Line
----------------	---------

Housing Features

Connector Style	Plug
Centerline (mm [in])	6.00 [0.236]
Housing Material	PBT GF
Housing Color	Yellow

Configuration Features

Number of Positions	3
---------------------	---

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Identification Marking

Keying	D
--------	---

Environmental

Operating Temperature (°C [°F])	-55 - +150 [-67 - +302]
Halogen Free	No

Conditions for Usage

Applies To	Wire/Cable
Glow Wire Rating	Standard Part - Not Glow Wire
For Use With	Receptacle (Socket) Contact, Cap Housing

Operation/Application

Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Power

Other

Brand	TE Connectivity
-------	-----------------

Related Products

Not quite the product
you're looking for?

[Find Similar Products](#)

[View Part in Product
Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

