**Part Number :** 334670004
**Product Description :** 2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 22 AWG, Left Reel Payoff,  Also used with MX123 Female Receptacle Housing
**Series Number :** 33467
**Status :** Active
**Product Category :** Crimp Terminals



## Documents and Resources

### Drawings

334670004_sd.pdf

PK-30907-759-001.pdf

313025040-000.pdf

PK-31302-480-001.pdf

### Specifications

AS-33468-001-001.pdf

PS-33468-001-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 34; 33 |
| China RoHS | Not Relevant |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Crimp Terminals |
| Series | 33467 |
| Description | 2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 22 AWG, Left Reel Payoff,  Also used with MX123 Female Receptacle Housing |
| Application | Automotive, Power, Wire-to-Board, Wire-to-Wire |
| Comments | Left Reel Payoff |
| Product Name | MX123,MX64 |
| UPC | 756054764053 |

### Physical

| | |
|---|---|
| Gender | Female |
| Material - Metal | Copper |
| Material - Plating Mating | Gold |
| Net Weight | 0.225/g |
| Packaging Type | Reel |
| Plating min - Mating | 0.762µm |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | 1.50-2.06mm |
| Wire Size (AWG) | 22 |

Downloaded from Arrow.com.

| | |
|---|---|
| Wire Size $mm^2$ | N/A |

### Solder Process Data

| | |
|---|---|
| Lead-Free Process Capability | N/A |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|---|---|
| MX64 Sealed Single Row Receptacle Housings | 31403 |
| MX123 Receptacle Housings | 34566 |
| MX123 Female Receptacle Housings | 34576 |

## Application Tooling

## Global

| Description | Part Number |
|---|---|
| FA2 Mechanical Feed Crimp Applicator for MX64 Grip Terminals, 22 AWG | 638088300 |
| PremiumGrade Hand Crimp Tool for 2.54mm MX64 Terminals, 22-18 AWG | 638114200 |
| Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals | 638131400 |



Downloaded from Arrow.com.