



Part Number : [194390008](#)

Product Description : Loxon Locking Quick Disconnect Housing, Nylon, UL94V-0, Natural

Series Number : 19439

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : LOCKQD V-0



Documents and Resources

Drawings

[194390008_sd.pdf](#)

[194390008-000.pdf](#)

Specifications

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19439
Description	Loxon Locking Quick Disconnect Housing, Nylon, UL94V-0, Natural
Product Name	Loxon
Style	Insulator Housing
Type	Loxon Locking Disconnect
UPC	193264611690

Agency

UL	E79133
----	--------

Electrical

Voltage - Maximum	600V AC
-------------------	---------

Physical

Barrel Type	N/A
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Capable	Yes
Insulated	N/A
Insulation	N/A
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.905/g

Orientation	Straight
Packaging Type	Carton
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Loxon Locking Quick Disconnect, Female, for 18-20 Wire, Reel, Tab 6.35 x 0.81mm	<u>194390001</u>
Loxon Locking Quick Disconnect, Female, for 18-20 Wire, Tab 6.35 x 0.81mm, Carton	<u>194390002</u>
Loxon Locking Quick Disconnect, Female, for 14-16 Wire, Reel, Tab 6.35 x 0.81mm	<u>194390003</u>
Loxon Locking Quick Disconnect, Female, for 14-16 Wire, Tab 6.35 x 0.81mm, Carton	<u>194390004</u>
Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm	<u>194390005</u>
Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Tab 6.35 x 0.81mm, Carton	<u>194390006</u>

This document was generated on Apr 11, 2026