





Color: ■ red



Dimensions in mm

Technical data	
Total number of potentials	1

Electrical data	
Rated current	20 A
Test voltage	42 V



Connection Data		
Connection technology	CAGE CLAMP®	
Strip length	9 ... 11 mm / 0.35 ... 0.43 inches	
Clamping units	1	
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG	
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG	

Physical data		
Width	8 mm / 0.315 inches	
Height	15 mm / 0.591 inches	
Depth	40 mm / 1.575 inches	

Material data		
Color	red	
Fire load	0.037 MJ	
Weight	3.9 g	

Commercial data		
Product Group	2 (Terminal Block Accessories)	
PU (SPU)	50 pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4045454293482	
Customs tariff number	85366990990	

Product Classification		
UNSPSC	39121421	
eCl@ss 10.0	27-44-03-13	
eCl@ss 9.0	27-44-03-13	
ETIM 9.0	EC002255	
ETIM 10.0	EC002255	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
CAS-No.	7439-92-1	
REACH Candidate List Substance	Lead	
RoHS Compliance Status	Compliant,With Exemption	
RoHS Exemption	6(c)	
SCIP notification number (Austria)	2539418b-58c0-4420-b110-a8f6ab77c7d3	
SCIP notification number (Belgium)	40b91dd3-96ec-45e4-98a3-341b4f102193	
SCIP notification number (Bulgaria)	2c7e6bcf-0e3a-4874-bd96-ca190e7a4a9e	
SCIP notification number (Czech Republic)	6ae9ae04-5491-4be6-9408-287c5cac46ef	
SCIP notification number (Denmark)	ee055b55-ddba-4b30-b59e-050f53013fbf	
SCIP notification number (Finland)	b9f0e73b-b87a-4d38-9f60-07226fdca07c	
SCIP notification number (France)	777cf7f1-adc1-488b-8b47-2ec5717e1dbc	
SCIP notification number (Germany)	f86c9c1d-6b5b-4fcb-967f-87dfd241ff49	
SCIP notification number (Hungary)	e64905c2-f29e-42da-ae87-c0d1394acf4c	
SCIP notification number (Italy)	3deffdb3-7962-4859-bb7b-d7bfa4bf193c	
SCIP notification number (Netherlands)	f5917138-401f-4204-8cee-f8469370655a	
SCIP notification number (Poland)	8d29f775-0f15-49b0-9c59-e38ab34f044f	
SCIP notification number (Romania)	1779a648-224f-4eb8-9cbf-7df1a926218b	
SCIP notification number (Sweden)	62c7a902-eab2-4325-8850-9887794132d4	



Downloads

Environmental Product Compliance

Compliance Search			
Environmental Product Compliance 215-212			↓

Documentation

Bid Text			
215-212	19.02.2019	xml 3.02 KB	↓
215-212	19.09.2017	doc 24.50 KB	↓


CAD/CAE-Data

CAD data	
2D/3D Models 215-212	↓

CAE data	
EPLAN Data Portal 215-212	↓
WSCAD Universe 215-212	↓


Installation Notes

Conductor termination



Conductor termination: Press button fully, insert stripped conductor into square entry and release.

Testing



Testing via banana plug.
Picture shows a test plug adapter (Item No. 209-170).

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com