
Part Number : 2169465111
Product Description : Ultra-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 22-20 AWG
Series Number : 216946
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

2169465111_sd.pdf

2169461000-PK-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

1723230003-000.pdf

2169461000-PS-000.pdf

2169460001-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	216946
Description	Ultra-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 22-20 AWG
Application	Wire-to-Wire
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Name	Ultra-Fit
UPC	195842154261

Agency

UL	E29179

Electrical

Voltage - Maximum	600V AC (RMS)/DC

Physical

Durability (mating cycles max)	200
Flammability	94V-0
Gender	Male
Material - Metal	Phosphor Bronze Alloy
Material - Plating Mating	Gold

Downloaded from Arrow.com.

Material - Plating Termination	Matte Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	0.380µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-1.50mm
Wire Size (AWG)	20, 22
Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Ultra-Fit Single Row Plug Housings	202569
Ultra-Fit Dual Row Plug Housings	216945

Application Tooling

Global

Description	Part Number
Extraction Tool for Ultra-Fit Plug Terminals, 18-16 AWG and 22-20 AWG Wires	2002221700
FineAdjust Applicator for Ultra-Fit Tangless Plug Terminals, 22-20 AWG, UL1061 Wire	2037024400
Hand Crimp Tool for Ultra-Fit Tangless Male and Female Terminals, 22-20 AWG (UL 1061) Wire	2238630900

Downloaded from Arrow.com.