


Side panels, Type F

SCHROFF



Other Views



Catalog Number: 34560-285

Back To Product

- Versions for EMC sealing (stainless steel or textile) side panels type F, 19" bracket, corner profile, EMC sealing, wall mounting, side panel linking, handles, panel fitting
- Flat side panel for separately screw-mountable 19" bracket

Product family:

EuropacPRO

Note:

Further components for construction of a shielded or unshielded subrack: 19" bracket, corner profile; Horizontal rails; Guide rails; Cover plates; Rear/front; Handles; EMC shielding; Internal assemblies

Type:

Individual Components

Individual Component Type:

Panels & Accessories



Select product specifications before modifying or adding to project list or requesting a quote.

Height-U-defining

4 ▾

Depth-mm-defining

175 ▾

[Clear Selection](#)

Quantity

1

Add Item to Project List +

Links



Native CAD files












Technical Data

Depth mm	175.0
Qty	1 piece
Description	Side panel
Description	without 19" bracket, Al, 2 mm, passivated, please order 19" bracket and corner profile separately
Height U	4

Delivery Comprises:

Item	Quantity	Description
1	1	Side panel, Al, 2 mm, chromated

Accessories

	Corner profile for EMC sealing (textile)	24564-299	Add Item to Project List +
	19" bracket type F with handle holes for textile sealing	24564-298	Add Item to Project List +
	19" bracket type F without handle holes for textile sealing	24564-297	Add Item to Project List +
	Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces	24560-155	Add Item to Project List +
	Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces	24560-297	Add Item to Project List +
	Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces	24560-298	Add Item to Project List +
	Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces	24560-299	Add Item to Project List +
	Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces	24561-298	Add Item to Project List +
	Side panel connecting bracket, between europacPRO subrack and fan, including fixing material kit, PU 4 pieces	21101-954	Add Item to Project List +
	Countersunk screw, torx (M4x14), steel zinc plated, PU 100 pieces	24560-130	Add Item to Project List +
	Stainless steel EMC gasket, 4 U, 142 mm, stainless steel, two pieces necessary per front panel, PU 10 pcs	21101-713	Add Item to Project List +
	EMC shielding textile gasket, -40...+70 °C, 4 U, PU 10 pcs	21101-858	Add Item to Project List +

EXPLORE

About Us

Services & Capabilities

Downloaded from [Arrow.com](https://www.arrow.com)

CONTACT

Customer Service

Find a Sales Office or Distributor

DOWNLOAD

Download Center

Reference Projects

[News & Events](#)

[Newsletter Subscriptions](#)

[Strategic Partnerships](#)

[Investor Relations](#)

[Global Locations](#)

[Product Compliance & Certifications](#)

[Partner Login](#)

[Videos](#)

[Product Configurators](#)

[Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

