


USB 3.0 SuperSpeed to DisplayPort Dual-Monitor Cable, 512 MB SDRAM, 2560 x 1600, 1080p

MODEL NUMBER: **U344-001-DP**



Add an additional Displayport Monitor or Projector through a single USB 3.0 port

Description

Tripp Lite U344-001-DP USB 3.0 SuperSpeed to DisplayPort Dual-Monitor Cable creates as an external DisplayPort video card via an available USB 3.0 port on your PC or Laptop. Connect up to six DisplayPort enabled monitors, with support for video resolutions up to 2560 x 1600 (1080p) and 5.1 surround sound audio.

Taking advantage of the SuperSpeed USB 3.0 interface (5Gbps), the external video graphics card adapter delivers smooth, high-definition content to your DisplayPort-capable display, and can be used to clone the image on multiple displays, or extended across them. Windows and Intel Mac compatible.

Features

- Adds an additional monitor, LCD or projector through a single USB 3.0 port
- USB 3.0 is 10 times faster than USB 2.0, with transfer rates up to 5 Gbps
- Backward compatible with USB 2.0
- Simultaneously connect up to 6 display adapters
- Automatically resumes from hibernation and suspend modes
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2560 x 1600 @ 60Hz
- Video streaming is supported up to 1080p
- Set additional monitors to extend the primary display, duplicate the primary display, or set an additional monitor as the primary display
- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8, 8.1 and 10.
- Compatible with Intel Mac OS X 10.8.5 and later, Mac 10.11. Supports both 32- and 64-bit.
- Mac OS X versions 10.8.5 and earlier do not support audio over USB 3.0. Mac OS X versions 10.7.x and earlier do not support USB 3.0.

Highlights

- Add an additional DisplayPort monitor through a single USB 3.0 port
- Windows and Intel Mac compatible
- Up to six adapters can be added to one computer
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2560 x 1600 @ 60Hz
- Compatible with Ubuntu 14.04.2

System Requirements

- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8, 8.1 and 10.
- Compatible with Intel Mac OS X 10.8.5 and later, Mac 10.11. Supports both 32- and 64-bit.
- Mac OS X versions 10.8.5 and earlier do not support audio over USB 3.0. Mac OS X versions 10.7.x and earlier do not support USB 3.0.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

Package Includes

- U344-001-DP USB 3.0 SuperSpeed to DisplayPort Dual-Monitor Cable
- Driver CD
- USB 3.0 Cable
- Owners Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Uses DisplayLink DL3500 chipset

Specifications

OVERVIEW	
UPC Code	037332180346
Technology	DisplayPort
VIDEO	
Max Supported Video Resolution	2560 x 1600 @60Hz
INPUT	
Bus Powered	Yes
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	1.00 x 5.00 x 6.00
Shipping Dimensions (hwd / cm)	2.54 x 12.70 x 15.24
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	0.750 x 2.250 x 3.250
Unit Packaging Type	Box
Unit Weight (lbs.)	0.10
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	0% to 90 RH, Non-Condensing
Operating Temperature	50 to 104 F (10 to 40 C)
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Displayport Specification	1.1a
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	Yes
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>