

BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD



**Image above is for illustration purpose only.*

ATS Part#:	ATS-50425B-C1-R0
Description:	42.50 x 42.50 x 7.50 mm BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD
Heat Sink Type:	maxiFLOW
Heat Sink Attachment:	maxiGRIP
Equivalent Part Number:	ATS-50425B-C2-R0


Features & Benefits

- maxiFLOW™ design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- maxiGRIP™ attachment applies steady, even pressure to the component and does not require holes in the PCB
- Meets Telcordia GR-63-Core Office Vibration; ETSI 300 019 Transportation Vibration; and MIL-STD-810 Shock and Unpackaged Drop Testing standards
- Comes preassembled with high performance thermal interface material
- Designed for standard height components from 3 to 4.5mm

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	4.3 °C/W	3.2 °C/W	2.8 °C/W	2.4 °C/W	2.2 °C/W	2.1 °C/W	1.9 °C/W
	Ducted Flow	3	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	42.50 mm	42.50 mm	7.50 mm	58.9 mm	T412	BLUE-ANODIZED
Notes: - Dimension A and B refer to component size. - Dimension C is the heat sink height from the bottom of the base to the top of the fin field. - ATS-50425B-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint-Gobain C675). - Thermal performance data are provided for reference only. Actual performance may vary by application. - ATS reserves the right to update or change its products without notice to improve the design or performance. - ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. - Optional maxiGRIP™ Installation/Removal Tool Set P/N: MGT425 - Contact ATS to learn about custom options available.						

**Image above is for illustration purpose only.*

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



Rev - 011018