



Part Number : [5024380000](#)

Product Description : CLIK-Mate 2.00mm Pitch Crimp Terminal, Male, Tin Plating, 26-22 AWG, Reel

Series Number : 502438

Status : Active

Product Category : Crimp Terminals

Packaging Alternative : [5024380100](#) (Bag)



Documents and Resources

Drawings

[5024380000_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-502439-001-001.pdf](#)

[AS-502439-002-001.pdf](#)

[SPK-502438-001-001.pdf](#)


[5024431570-000.pdf](#)

Tooling Specifications

[CS-502438-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	502438
Description	CLIK-Mate 2.00mm Pitch Crimp Terminal, Male, Tin Plating, 26-22 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	CLIK-Mate
UPC	822350909778

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.5mm
Wire Size (AWG)	22, 24, 26
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
2.00mm Pitch CLIK-Mate Single Row Plug Housings	502439

Application Tooling

Global

Description	Part Number
Extraction and Activation Tool	638132700
Hand Crimp Tool for 2.00mm Pitch Wire-to-Board Crimp Terminals, 26-22 AWG Wire	638192800
FineAdjust Applicator for CLIK-Mate Terminals, for 26-22 AWG Wire with Insulation Diameter 0.90-1.50mm	639007700
T2 Terminator Tooling Die for 2.00mm Crimp Terminal, 26-22 AWG	639107700

Japan

Description	Part Number
S-1 Applicator for CLIK-Mate Terminals, 26-22 AWG	5780453700

This document was generated on Mar 02, 2026