


Data Sheet | Item Number: 890-623


Mounting plate; 3-pole; for distribution connectors; Plastic; black

<https://www.wago.com/890-623>



Color: ■ black

Dimensions in mm



Dimensions in mm

Mounting accessories WINSTA® MINI 3-pole

Realize the electrical installation easily and quickly: The mounting accessories from the *WINSTA®* MINI product line is the product of your choice for error-free electrical installation. An extensive range of accessories complements the *WINSTA®* product line from WAGO. Thanks to its particularly compact dimensions, our *WINSTA®* MINI Pluggable Connection System with Push-in *CAGE CLAMP®* spring pressure connection technology is very suitable in very tight spaces, i.e., for connections when very little room is available.

WINSTA® MINI solutions for your electrical installation – protected against mismatching and maintenance-free

WINSTA® is the pluggable connection system that is ideally tailored to the strict requirements of electrical installation. It ensures error-free installation of cables and components, quickly and reliably. Choose quality and durability – with protection against mismatching from WAGO makes the installation of electrical components noticeably easier.

- easy tool-free operation, a wide range of coding options
- rapid, structured electrical installation



Notes	
General safety information	NOTICE: Observe installation and safety instructions! 1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100). 2. Do not install while energized or under load. 3. Use only for its intended purpose. 4. Observe applicable national regulations, standards and directives. 5. Observe the technical specifications of the products. 6. Ensure correct polarity assignment. 7. Do not use damaged or contaminated components. 8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters. 9. Insert conductors up to the stop. 10. Use only with locking lever and strain relief. 11. Use original accessories only. To be sold only with installation instructions!

Connection Data	
Connection 1	
Pole number	3

Physical data	
Width	21.4 mm / 0.843 inches
Height	13 mm / 0.512 inches
Depth	25 mm / 0.984 inches

Mechanical data	
Mounting type	Screw mount
Suitable	for distribution connectors (except T-distribution connectors); 3-pole

Material data	
Note (material data)	Information on material specifications can be found here
Color	black
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.052 MJ
Weight	1.9 g

Environmental requirements	
Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C



Commercial data		
Product Group		20 (Winsta)
PU (SPU)		50 pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454684594
Customs tariff number		39269097900

Product Classification		
UNSPSC		39121321
eCl@ss 10.0		27-44-06-92
eCl@ss 9.0		27-44-06-92
ETIM 9.0		EC002863
ETIM 10.0		EC002863
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Approvals / Certificates		
Approvals for marine applications		



Approval	Standard	Certificate Name
LR Lloyds Register	EN 61535	LR23317167TA

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 890-623		

Documentation			
Bid Text			
890-623	11.03.2015	doc 21.50 KB	
890-623	19.02.2019	xml 2.55 KB	



CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 890-623	WSCAD Universe 890-623
	
	ZUKEN Portal 890-623
	