

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Contact carrier, 8-position, Socket, straight, M12, coding: A , PCB mounting, SMD reflow, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1308214

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial Data

| | |
|--------------------------------------|---------------|
| Item number | 1412008 |
| Packing unit | 1 pc |
| Minimum order quantity | 100 pc |
| Sales Key | AB23 |
| Product Key | ABQBGH |
| GTIN | 4046356992817 |
| Weight per Piece (including packing) | 6.21 g |
| Weight per Piece (excluding packing) | 6.21 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

Technical Data

Notes

| | |
|---------|--|
| General | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|---------|--|

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Number of positions | 8 |
| Application | Signal |
| Seal present | yes |
| Shielded | yes |
| Coding | A |
| Thread type | M12 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------|----------------------------|
| Rated surge voltage | 0.8 kV |
| Contact resistance | $\leq 3 \text{ m}\Omega$ |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 30 V |
| Nominal current I_N | 2 A |

Material specifications

| | |
|--|------|
| Flammability rating according to UL 94 | V0 |
| Seal material | FKM |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA |

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | A |

Mechanical properties

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier

1412008

<https://www.phoenixcontact.com/us/products/1412008>



Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Degree of protection (when plugged in) | IP67 (correctly plugged in and locked) |
| Degree of protection | IP67 |
| Ambient temperature (operation) | -25 °C ... 105 °C (Plug / socket) |
| | -40 °C ... 105 °C (without mechanical actuation) |

Standards and regulations

M12

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |
| Note | In line with |

Mounting

| | |
|-------------------|--------------|
| Mounting type | PCB mounting |
| Connection method | SMD reflow |

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier


1412008

<https://www.phoenixcontact.com/us/products/1412008>



Drawings

Dimensional drawing



SMD tape-on-reel packing


SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier

1412008

<https://www.phoenixcontact.com/us/products/1412008>




Dimensional drawing



View of solder side

Drilling plan/solder pad geometry



Soldering pad geometry


SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008


<https://www.phoenixcontact.com/us/products/1412008>

Dimensional drawing



Dimensional drawing

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

1412008

<https://www.phoenixcontact.com/us/products/1412008>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412008>

| | |
|---|------------------------------------|
|  | EAC Approval ID: B.01687 |
|---|------------------------------------|

|  | cULus Recognized | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal Voltage U_N | Nominal Current I_N | Cross Section AWG | Cross Section mm^2 |
| | 30 V | 2 A | - | - |

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier

1412008

<https://www.phoenixcontact.com/us/products/1412008>



Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

China RoHS

Environmentally Friendly Use Period = 50 years

For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

Accessories

SACC-CIP-M12FS-8P SMD SH-SP - Sample set

1418636

<https://www.phoenixcontact.com/us/products/1418636>



Sample set, 8-position, Socket, straight, M12, coding: A , PCB mounting, SMD,
Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%)
item no.: 1239201

SACC-BP-F-M12/M15-6-SMD - Housing screw connection

1414021

<https://www.phoenixcontact.com/us/products/1414021>



Housing screw connection, Socket, M12, Rear mounting, Alternative product in
accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1239058

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection

1414023

<https://www.phoenixcontact.com/us/products/1414023>



Housing screw connection, Socket, M12-SPEEDCON, Rear mounting, M15 x 1,
Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%)
item no.: 1239059

SACC-FP-F-M12/M14 SMD - Housing screw connection

1412079

<https://www.phoenixcontact.com/us/products/1412079>

M12 female connector, front mounting SMD with M14 screw fastening



SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

SACC-FP-F-M12/PRESS SMD - Housing screw connection

1412081

<https://www.phoenixcontact.com/us/products/1412081>

Housing screw connection, Socket, M12, Front mounting, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1238973



SACC-BP-F-M12/SMD-0,9/1,6-9TIP - Housing screw connection

1419569

<https://www.phoenixcontact.com/us/products/1419569>

Housing screw connection, M12, Rear mounting, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1239268



SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

SACC-BP-F-M12/SMD-1,6/2,3-9TIP - Housing screw connection

1419570

<https://www.phoenixcontact.com/us/products/1419570>

Housing screw connection, M12, Rear mounting



SACC-BP-F-M12/SMD-2,3/3,0-9TIP - Housing screw connection

1419571

<https://www.phoenixcontact.com/us/products/1419571>

Housing screw connection, M12, Rear mounting, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1239270



SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

SACC-BP-F-FIX/NUT-BK-SMD - Fixing sleeve

1419568

<https://www.phoenixcontact.com/us/products/1419568>



Fixing sleeve for M12 housing screw connection with tolerance-compensating function, for SMD-solderable M12 socket contact inserts.

SACC-BP-F-FIX/NUT-CY-SMD - Fixing sleeve

1419565

<https://www.phoenixcontact.com/us/products/1419565>



Fixing sleeve for M12 housing screw connection with tolerance-compensating function, for SMD-solderable M12 socket contact inserts.

SACC-CIP-M12FS-8P SMD SH R32 - Contact carrier



1412008

<https://www.phoenixcontact.com/us/products/1412008>

SACC-BP-F-FIX/NUT-GN-SMD - Fixing sleeve

1419566

<https://www.phoenixcontact.com/us/products/1419566>



Fixing sleeve for M12 housing screw connection with tolerance-compensating function, for SMD-solderable M12 socket contact inserts.

SACC-BP-F-FIX/NUT-VT-SMD - Fixing sleeve

1419567

<https://www.phoenixcontact.com/us/products/1419567>



Fixing sleeve for M12 housing screw connection with tolerance-compensating function, for SMD-solderable M12 socket contact inserts.

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com