


# Active GPS Antenna

Pulse Part Number GPSGM Family



The GPSGM family of active GPS ultra thin, oval shaped antennas offer versatility for installation, as they can be positioned on the dash or window without orientation concerns

**Features**

- 50 percent thinner than standard GPS antennas
- Versatile installation inside the vehicle - no specific installation location or orientation required.
- Glass or dashboard mount
- Offered with a variety of cable lengths and connector options
- RoHS Compliant Product

**Applications**

- Vehicle tracking
- Fleet management / asset tracking
- In-car infotainment
- “Pay-as-you-drive” insurance applications

P/N	Cable Length (feet / meters)	Connector
GPSGMSMA	16.4 / 5	SMA Male

# Active GPS Antenna

Pulse Part Number GPSGM Family

## Electrical Specifications

Frequency [MHz]	1575.42
Nominal Impedance [ $\Omega$ ]	50
VSWR Max	1.5:1
Gain [dBi Max]	1.5
Radiation Pattern	Omni-directional
Cable Type	RG-174

## LNA Specifications

Gain [dB $\pm$ 2]	26
Noise Figure [dBi]	1 Max
Current Draw [mA]	12 typical
Voltage [Dc]	3 - 5 ( $\pm$ 10%)

## Mechanical Specifications

Radome Material	PC-ABS Plastic Blend
Color	Black
Height [Inches/Meters]	.2 / 5.45
Width [Inches/Meters]	1.18 x 2 / 30 x 50
Mounting	Die cut double-sided tape included

## Environmental Specifications

Operating Temperature [ $^{\circ}$ C]	-40 to +85
Storage Temperature [ $^{\circ}$ C]	-40 to +85
Relative Humidity [%]	20 to 95

San Diego, CA 858 674 8100

Vancouver, WA 360 944 7551

Europe 49 7032 7806 0

Asia 86 755 33966678

North Asia 886 3 4356768


China 86 512 6807 9998

# Active GPS Antenna


Pulse Part Number GPSGM Family

## Radiation Patterns


**XZ Plane**



**ZY Plane**



**XY Plane**



## For More Information

### Pulse Worldwide Headquarters

12220 World Trade Drive  
San Diego, CA 92128  
U.S.A.

Tel: 858 674 8100  
Fax: 858 674 8262

### Larsen Brand Antennas

3611 NE 112th Avenue  
Vancouver, WA 98682  
USA

Tel: 360 944 7551  
Fax: 360 944 7556

### Europe Headquarters

Pulse GmbH & Co. KG  
Zeppelinstrasse 15  
Herrenberg  
Germany

Tel: 49 7032 7806 0  
Fax: 49 7032 7806 135

### Asia Headquarters

B402, Shenzhen Academy of  
Aerospace Technology Bldg.  
10th Kejian Road, High-Tech Zone  
Nanshan District, Shenzhen, PR China 518057

Tel: 86 755 33966678  
Fax: 86 755 33966700

### Pulse North Asia

3F, No. 198, Zhongyuan Road  
Zhongli City, Taoyuan County 320  
Taiwan R. O. C.

Tel: 886 3 4356768  
Fax: 886 3 4356823

### Pulse (Suzhou) Wireless Products Co., Inc.

99 Huo Ju Road, (#29 Bldg, 4th Phase)  
Suzhou New District  
Science & Tech Industrial Park  
Jiangsu Province, Suzhou 215009 PR China

Tel: 86 512 6807 9998  
Fax: 86 512 6809 8023

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2010. Pulse Electronics, Inc. All rights reserved.