Part Number : 11030036
Product Description : Extraction Tool for SL Terminals, 36-22 AWG
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : HT71800



Documents and Resources

Tooling Specifications

ATS-011030036-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Extraction Tool for SL Terminals, 36-22 AWG
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800753609525
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex

Downloaded from Arrow.com.

	and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Reel	16020069
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	16020082
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	16020083
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG, Reel	16020119
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Reel	16021112
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 30-24 AWG, Reel	16021113
SL Crimp Terminal, Female, 30-24	700580082

Downloaded from Arrow.com.

AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	
SL Crimp Terminal, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	700580083
SL Crimp Terminal, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Reel	700581069

Downloaded from Arrow.com.