


SmartRack Roof-Mounted Cable Trough Vertical Expansion Plates - Requires SRCABLETRAY

MODEL NUMBER: **SRCABLETRAYEXP**



Highlights

- Adds an additional level of cable routing to the SRCABLETRAY
- When used with the SRCABLETRAY these expansion plates allow dedicated, separate paths for power, data and fiber cables
- Helps eliminate cable stress
- Organizes cables outside of SmartRack enclosure
- Toolless mounting on the SmartRack enclosure's top panel

Package Includes

- SRCABLETRAYEXP expansion sections (2)
- #8-32 x 1/4 Phillips Screws (8)

Description

SmartRack® SRCABLETRAYEXP adds an additional level of cable routing to the SRCABLETRAY (required part). When used with the SRCABLETRAY, these expansion plates allow dedicated, separate paths for power, data and fiber cables. The SRCABLETRAYEXP helps eliminate cable stress by organizing cables outside of the SmartRack enclosure. Convenient, toolless mounting on the top panel of the SmartRack enclosure.

Features

- SmartRack SRCABLETRAYEXP adds an additional level of cable routing to the SRCABLETRAY (required part)
- When used with the SRCABLETRAY these expansion plates allow dedicated, separate paths for power, data and fiber cables
- The SRCABLETRAYEXP helps eliminate cable stress by organizing cables outside of the SmartRack enclosure
- Convenient, toolless mounting on the top panel of the SmartRack enclosure

Specifications

OVERVIEW	
UPC Code	037332140791
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.30 x 12.10 x 21.80
Shipping Dimensions (hwd / cm)	8.38 x 30.73 x 55.37
Shipping Weight (lbs.)	8.80



Powering Business Worldwide



Shipping Weight (kg)	3.99
Unit Dimensions (hwd / in.)	2.200 x 12.130 x 21.140
Unit Dimensions (hwd / cm)	5.59 x 30.81 x 53.70
Unit Weight (lbs.)	4
Unit Weight (kg)	1.81
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.