



[Labels](#) / [Wire and Cable Labels](#) / [Wire and Cable Label Cards](#) /

Pre-printed 6 Wire Markers



## Pre-printed 6 Wire Markers

**Part Number:**

TMM-6-PK

**Dimensions:**

0.5 in H

**Material:**

Vinyl

**Color:**

Black on White

**Text Legend:**

6

PEOPLE ALSO VIEWED



OVERVIEW

B-702 Low-Profile Glossy Vinyl-Coated Polyester miniature wire markers from Brady® have high adhesion properties, making them ideal for wire marking and machine tool labeling.

- Card-mounted wire markers allow for quick, on-the-spot wire marking
- Glossy white vinyl topcoat with a high tack rubber-based adhesive features excellent flexibility for wrapping on thin gauge wire
- High adhesion and low profile when wrapped on wires
- Withstands mild chemicals, oil and water

SPECIFICATIONS

|                                |                  |
|--------------------------------|------------------|
| Material Number                | B-702            |
| Cards or Sheets per Pack       | 25               |
| Dimensions                     | 0.5 in H         |
| UOM                            | Pack of 25 Cards |
| Finish                         | Gloss            |
| Maximum Service Temperature °F | 212 °F           |
| Minimum Service Temperature °F | -40 °F           |
| Product Number                 | 111468           |
| UPC                            | 662820905004     |

|                            |                                                                                                             |
|----------------------------|-------------------------------------------------------------------------------------------------------------|
| Quantity per Card or Sheet | 150                                                                                                         |
| Thickness                  | 0.0022 in                                                                                                   |
| Adhesive Type              | Rubber                                                                                                      |
| Applications               | Cable & Wire Marking, Machine Tool Labeling                                                                 |
| Color                      | Black on White                                                                                              |
| Label/Media Format         | Die-Cut on Cards                                                                                            |
| Material                   | Vinyl                                                                                                       |
| Material Properties        | Low Profile                                                                                                 |
| Resistance Properties      | Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant, Weather-Resistant |
| Serialization              | No Serialization                                                                                            |
| Text Legend                | 6                                                                                                           |

## Solutions

[Floor Marking Guide](#)  
[GHS Label Compliance](#)  
[Lockout Tagout Compliance](#)  
[Arc Flash Labeling Requirements](#)  
[Cable and Wire Label Options](#)  
[Product and Barcode Labeling](#)  
[Brand Protection Solutions](#)

## Services

[Lockout Tagout Services](#)  
[Arc Flash Services](#)  
[Confined Space Services](#)  
[Visual Workplace Services](#)  
[Hazcom GHS Services](#)  
[Software Programming & Integration](#)  
[Label Template & File Conversion](#)  
[Printer Use & Training](#)  
[Printer Preventative Maintenance](#)  
[Toll and Custom Coating](#)  
[Authentication & Tracking Services](#)

## Help

[Contact Us](#)  
[Knowledge Center](#)  
[Printer Drivers & Firmware](#)  
[Brady Software Updates](#)  
[Safety Data Sheets](#)  
[Technical Data Sheets](#)  
[WEEE-RoHS Compliance](#)  
[Product Certification](#)  
[Printer Registration](#)

## Resources

[Find a Distributor](#)  
[Printer Selection Tool](#)  
[Label Selection Tool](#)  
[Digital Catalog](#)  
[Request a Catalog](#)  
[Interactive Facility Map](#)




**Brady**  
**(NYSE:BRC)**  
 is a  
 manufacturer  
 of complete  
 solutions  
 that  
 identify and  
 protect  
 people,  
 products  
 and places.  
 Brady's  
 products  
 help  
 customers  
 increase

**Contact**  
 6555  
 W.  
 Good  
 Hope  
 Rd.  
 Milwaukee  
 WI  
 53223  
 Phone:  
 888-  
 250-  
 3082  
 Hours:  
 7am-  
 6pm  
 CST

**About**  
[Corporation](#)  
[Privacy](#)  
[Policy](#)  
[Terms](#)  
 and  
[Conditions](#)  
[Terms](#)  
[of Use](#)  
[ISO](#)  
[Certificates](#)

**Other**  
**Brady**  
**Sites**  
**Distributor**  
**Portal**  
**International**  
**Sites**  
**Safety**  
**Services**  
 &  
**Software**  
**Smart**  
**ID**  
**Brand**  
**Protection**



2018 Brady Worldwide, Inc.

**safety,  
security,  
productivity  
and  
performance  
and include  
high-  
performance  
labels,  
signs, safety  
devices,  
printing  
systems  
and  
software.**

**Monday  
-  
Thursday;  
Friday  
7am-  
5pm  
CST**