

Connectors > Rectangular Connectors > Rectangular Contact Inserts

1-1191440-5 ✓ ACTIVE

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 5 Position, Sealable, 16 AWG Wire Size, 1.5 mm² Wire Size, 1.5 A



RAYCHEM

TE Internal #: 198805-000
TE Internal Description: MTCP-116-05P2
Mil-Spec: B: MTCP116-05P2

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : 5
Centerline (Pitch) : **1.27 mm [.05 in]**

Add to List ▾ | Similar Products | Digital Datasheet

Compatible Parts & Tooling

Documents	Features	Product Compliance
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.		
Product Type Features	Rectangular Connector Insert Type : Insert for Contacts Connector System : Wire-to-Wire Sealable : Yes Connector & Contact Terminates To : Wire & Cable	
Configuration Features	Number of Positions : 5	
Body Features	Primary Product Color : Black Primary Product Material : High Grade Polyarylene Thermoplastic Seal Type : Grommet Seal, Interfacial Seal	
Contact Features	Contact Type : Pin Contact Current Rating (Max) (A): 1.5	
Mechanical Attachment	Polarization Code : A/B Connector Mounting Type : Panel Mount	
Housing Features	Centerline (Pitch) : 1.27 mm [.05 in]	
Dimensions	Wire Size (AWG): 16 Wire Size (mm²): 1.5	
Usage Conditions	Operating Temperature Range : -65 – 125 °C [-85 – 257 °F]	
Operation/Application	Compatible With Connector Shell Size : 50.8 [2.0]	

SHOP OUR DISTRIBUTORS

North America ▾

See all price breaks

Distributor	1	10,000	Buy
TTI, Inc. 48 in-stock	\$308.780	\$308.780	SHOP NOW
DigiKey Electronics 24 in-stock	\$272.500	\$243.436	SHOP NOW
BJG Electronics Inc 24 in-stock			Visit Site

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

REPORT PRODUCT DATA ERROR

Compatible Parts

There are no compatible parts for this product.
Please reach out to Product Support to help with your request.

> [Contact Product Support](#)

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RECTANGULAR CONTACT INSERTS
1-1191440-5
Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 5...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : 5
Centerline (Pitch) : **1.27 mm**

TOP RESULTS

RECTANGULAR CONTACT INSERTS
1-1196320-6
Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 5...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : 5
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS
2-1191312-8
Rectangular Contact Inserts, Insert for Contacts, Socket, Wire-to-Wire, 5...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : 5
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS
7-1194775-9
Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : 20
Centerline (Pitch) : **1.27 mm**

Customers Also Bought

TE Part #: **202F221-51/86-0**
Heat Shrink Boots, Straight, Size 202, Lipped, 51, 20...

\$38.200 per unit
Inventory: In-Stock
[Add To Cart](#)

TE Part #: **2-1191312-8**
Rectangular Contact Inserts, Insert for Contacts, Socket...

[View Product](#)

TE Part #: **MTCP-122-20PQ**
Rectangular Contact Inserts, Insert for Contacts, Pin...

[View Product](#)

TE Part #: **9-1191856-4**
Rectangular Contact Inserts, Insert for Contacts, Socket...

[View Product](#)

TE Part #: **SO175-1-01**
SolderSleeve Shield Terminators, 1.91 mm [.075...

[View Product](#)

TE Par
023 [V
Stand
Conne

[View Product](#)

Contact Our Team – 24/7 Support

+1 800 522 6752

Live Chat

[See Support Details](#)

Connect With Us

Access Partner Information

[Distributors](#)

[Suppliers](#)

[Supplier Diversity](#)

Get Answers Now

[Authorized Distributors & Resellers](#)

[Product FAQs](#)

[Samples FAQs](#)

[TE Store FAQs](#)

[Terms and Conditions of Sale](#)

[Samples Terms and Conditions](#)

Select Your Preferences

Language

English (EN)

Ship to

United States (\$USD)