



PC Mount

PC pins eliminate wiring. Solders directly to PC for compact applications.



PC Mount with Ribbon (RB)

Ribbon wraps under batteries during battery installation. For easy battery removal, pulling up on ribbon will dislodge batteries from holder.



6" Wire Leads

Allows battery holder to be placed remotely from PC freeing up valuable board space.



6" Wire Leads with 3 Pin Locking PC Connector (CN)

PC connector eliminates hand soldering of wire leads to PC. Battery holder can be quickly added or removed from PC.

- Coil spring contacts will adjust to different battery lengths
- Batteries securely held in place to assure a positive connection and low contact resistance
- Withstands shock and vibration
- Holders for multiple cell are prewired in series
- Custom designs welcome, Ex: Parallel wiring, custom wiring, combining any of the available options

SPECIFICATIONS

Base: Polypropylene

Spring: Spring Steel, Nickel Plate

PC Pins: Brass, Nickel Plate


Wire Leads: 6.0 (152), #26 AWG Stripped and Tinned, UL/CSA 1007

Ribbon: Woven Nylon, Red

PC Connector: Nylon 6/6, Phosphor Bronze, Tin Plate


"AA"

One (1) Cell




CAT. NO. 2460	PC Mount
CAT. NO. 2460RB	PC Mount w/Ribbon
CAT. NO. 2461	Wire Leads Only
CAT. NO. 2461CN	Leads w/PC Connector

Two (2) Cells - In Series




CAT. NO. 2462	PC Mount
CAT. NO. 2462RB	PC Mount w/Ribbon
CAT. NO. 2463	Wire Leads Only
CAT. NO. 2463CN	Leads w/PC Connector

Three (3) Cells - In Series



CAT. NO. 2464	PC Mount
CAT. NO. 2464RB	PC Mount w/Ribbon
CAT. NO. 2465	Wire Leads Only
CAT. NO. 2465CN	Leads w/PC Connector


Four (4) Cells - In Series



CAT. NO. 2477	PC Mount
CAT. NO. 2477RB	PC Mount w/Ribbon
CAT. NO. 2478	Wire Leads Only
CAT. NO. 2478CN	Leads w/PC Connector


"AAA"

One (1) Cell




CAT. NO. 2466	PC Mount
CAT. NO. 2466RB	PC Mount w/Ribbon
CAT. NO. 2467	Wire Leads Only
CAT. NO. 2467CN	Leads w/PC Connector

Two (2) Cells - In Series




CAT. NO. 2468	PC Mount
CAT. NO. 2468RB	PC Mount w/Ribbon
CAT. NO. 2469	Wire Leads Only
CAT. NO. 2469CN	Leads w/PC Connector

Three (3) "AAA" Cells - In Series



CAT. NO. 2479	PC Mount
CAT. NO. 2479RB	PC Mount w/Ribbon
CAT. NO. 2480	Wire Leads Only
CAT. NO. 2480CN	Leads w/PC Connector


Four (4) Cells - In Series



CAT. NO. 2481	PC Mount
CAT. NO. 2481RB	PC Mount w/Ribbon
CAT. NO. 2482	Wire Leads Only
CAT. NO. 2482CN	Leads w/PC Connector

ECONOMICAL PLASTIC BATTERY HOLDERS (CONT'D)


"1/2 AA" Cell -or- "CR2" Cell



CAT. NO. 2485	PC Mount
CAT. NO. 2485RB	PC Mount w/ribbon
CAT. NO. 2486	6" Wire Leads - 6.0 (152)
CAT. NO. 2486CN	Wire Leads w/PC Connector


"1/2AA" - "CR2" - "N" - "12V"

"N" Cell - 1.5V or "12V" Cell



CAT. NO. 2470	PC Mount
CAT. NO. 2470RB	PC Mount w/ribbon
CAT. NO. 2471	6" Wire Leads - 6.0 (152)
CAT. NO. 2471CN	Wire Leads w/PC Connector

Two (2) "N" or Two (2) "12V" Cells - In Series



CAT. NO. 2472	PC Mount
CAT. NO. 2472RB	PC Mount w/ribbon
CAT. NO. 2473	6" Wire Leads - 6.0 (152)
CAT. NO. 2473CN	Wire Leads w/PC Connector

PLASTIC BATTERY HOLDERS WITH SNAP-ON CONNECTORS

- Same quality features as our wired & PC mount battery holders
- Features separable "Snap-On/Snap-Off" battery connector (9 Volt type) to assure reliable connections
- Easily disconnect battery holder from your device - no tools required
- Batteries securely held in place to maintain a positive contact and a low contact resistance

- Battery contact springs self adjust to variations in battery length
- Mates with Keystone 9 Volt battery straps and connectors (Refer to pages 36)

SPECIFICATIONS


Holder: Polypropylene

Male/Female Contacts: Brass, Nickel Plate

Springs: Spring Steel, Nickel Plate


"AA"

Two Cells - in Series




CAT. NO. 2474

Three (3) Cells - in Series



CAT. NO. 2475

Four (4) Cells - in Series



CAT. NO. 2476

PC BATTERY HOLDER CONNECTOR JACKS

- Available in SMT and THM versions
- Vertical and horizontal entry options
- SMT version supplied on tape and reel for vacuum pick and place assembly
- Used to connect any battery holder with PC connector (CN suffix)
- Wiring harness locks onto jack for assured connectivity

SPECIFICATIONS

Body: Nylon 6/6, UL94V-0

Pins: Brass, Tin Plate


Current Rating: 3 Amps, 100V max

Temperature Range: -13°F (-25°C) to 185°F (85°C)

SMT

SUPPLIED ON TAPE AND REEL


VERTICAL



CAT. NO. 974

Tape and Reel Spec's: 13 inch reel (500 pieces per reel)

HORIZONTAL




CAT. NO. 976

Tape and Reel Spec's: 13 inch reel (1000 pieces per reel)


THM

VERTICAL



CAT. NO. 975

HORIZONTAL



CAT. NO. 977