


[→ Honeywell.com](#) [→ Automation & Control Solutions](#)
[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)

L

## Honeywell Sensing and Control



Search

**11TW8-3**

(Home : Products : Switches &gt; MICRO SWITCH™ Toggle Switches &gt; TW )

**narrow your search****Products**

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

**Technology**

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

**new products****New Wireless Products**


Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)**white papers**

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters




TW Series Toggle Switch, 1 pole, 2 position, Solder terminal, Standard Lever

*Actual product appearance may vary.*

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)
**Product Specifications**

Circuitry/Operating action

**Keyway Position**  
**Opposite Keyway Position**



Product Type

MICRO SWITCH™ Toggle Switch

Ampere/Voltage Range (Resistive Load)

0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc, 0.1 A to 5.0 A at 0.5 Vac to 115 Vac

Circuitry

SPDT

Action

2 position

Mounting

Bushing 15/32 in

Termination

Solder

Lever Type

Standard

UL/CSA

L117: 5 A at 125 Vac

Comment

Gold Plated Contacts

Availability

Global

UNSPSC Code

30211908

UNSPSC Commodity

30211908 Toggle switches

Series Name

TW

**Customer Service**

Technical Support

Global Sales &amp; Service

View Site Demo

Site Comments?

**meet dr. larry**

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.

[Meet Dr. Larry](#)**my links**[Login to iCOM](#)[Login to Rep/AD Portal](#)[Login to Digital University](#)**News Center**

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

**MICRO SWITCH Anniversary site****Need help?**[Click here to contact us](#)
[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)