

Product Lines

- AC Receptacles
- Cable Assemblies
- Cable Ties
- EM Power Line Filters
- AC & DC Fans
- Fan Accessories
- Heat Shrink Products
- Power Cords & Wiring Devices
- Power Supplies
- LED Products
- Thermal Circuit Breakers
- International Procurement



Full Line Stocking Distributor

Latest News



Press Releases
Posted on February 24, 2015



New Centrifugal Fans
Posted on Nov. 14, 2014



Click Here to see our
new line of Desktop,
Wall Mount, & Medical
Power Supplies
Posted on Apr. 14, 2014

Translate this page

Spanish

Microsoft® Translator


Home » Power Cords and Wiring Devices » North American Power Cords

Cross Reference Guide

Power Cord Inquiry Sheet

Power Cord Brochure

2 and 3 Conductor North American Power Cords



Images shown are for representation only, exact specs shown on PDF files.

Part Number	Fig.	Length	AWG	Amp	Cordage	Plug Type	Conn Type	Stock Check
2 Conductor Power Cords								
220002-01	A	9'0"	18	10	SPT-1	1-15P	Split	√
221001-01	A	6'0"	18	10	SPT-1	1-15P*	Split	√
221001-03	A	6'0"	18	10	SPT-1	1-15P*	Split	√
221001-08	A	6'0"	18	10	SPT-1	1-15P*	Split	√
221002-01	A	9'0"	18	10	SPT-1	1-15P*	Split ♦	√
223020-01•	B	6'0"	18	7	SPT-2	1-15P	C7	√
223021-01•	B	8'0"	18	7	SPT-2	1-15P	C7	√
223082-01•	B	6'0"	18	7	SPT-2	1-15P*	C7*	√
223083-01•	B	8'0"	18	7	SPT-2	1-15P	C7	√

3 Conductor Power Cords with North American Color Code								
211011-01	C	6'0"	18	10	SVT	5-15P	RQJ	√
211011-06	C	6'0"	18	10	SVT	5-15P	RQJ	√
211012-06	C	8'0"	18	10	SVT	5-15P	RQJ	√
211017-06	C	6'0"	18	10	SJT	5-15P	RQJ	√
211018-06	C	8'0"	18	10	SJT	5-15P	RQJ	√
212004-01	C	7'6"	18	10	SVT	5-15P	C13	√
212013-01	C	7'6"	16	13	SJT	5-15P	C13	√
212099-01	C	6'0"	18	10	SVT	5-15P	C13	√
225003-01	D	8'2"	14	15	SJT	5-15P	C19	√
226003-01□	E	8'2"	14	15	SJT	6-15P	C19	√
227003-01•	F	8'2"	12	20	SJT	5-20P	C19	√
228003-01□	G	8'2"	12	20	SJT	6-20P	C19	√

3 Conductor Power Cords with CEE Color Code								
311007-01	C	6'7"	18	10	SVT	5-15P	RQJ	√
311010-01	C	9'10"	18	10	SVT	5-15P	RQJ	√
311013-01	C	6'7"	18	10	SJT	5-15P	RQJ	√
311016-01	C	9'10"	18	10	SJT	5-15P	RQJ	√
311019-01	C	6'7"	16	13	SJT	5-15P	RQJ	√
311022-01	C	9'10"	16	13	SJT	5-15P	RQJ	√
311024-01	C	6'7"	14	15	SJT	5-15P	RQJ	√
311027-01	C	9'10"	14	15	SJT	5-15P	RQJ	√
311030-01•	C	6'7"	18	10	SJT	5-15P	RQJ	√
311275-01	C	12'0"	18	10	SJT	5-15P	RQJ	√
311276-01	C	15'0"	18	10	SJT	5-15P	RQJ	√
312003-01	C	7'6"	18	10	SVT	5-15P	C13	√
312003-06	C	7'6"	18	10	SVT	5-15P	C13	√
312007-01	C	6'7"	18	10	SJT	5-15P	C13	√
312008-01	C	7'6"	18	10	SJT	5-15P	C13	√
312010-01	C	9'10"	18	10	SJT	5-15P	C13	√
312011-01	C	6'7"	16	13	SJT	5-15P	C13	√

312014-01	C	9'10"	16	13	SJT	5-15P	C13	√
312016-01	C	6'7"	14	15	SJT	5-15P	C13	√
312019-01	C	9'10"	14	15	SJT	5-15P	C13	√
312021-01•	C	7'6"	18	10	SVT	5-15P	C13	√
312126-01	C	12'0"	18	10	SJT	5-15P	C13	√
312127-01	C	15'0"	18	10	SJT	5-15P	C13	√
312128-01•	C	6'0"	18	10	SVT	5-15P	C13	√
313001-01	C	7'6"	18	10	SVT	5-15P	C13 RA+	√
313003-01	C	6'7"	18	10	SVT	5-15P	C13 RA+	√
313006-01	C	6'7"	18	10	SJT	5-15P	C13 RA+	√
313009-01	C	9'10"	18	10	SJT	5-15P	C13 RA+	√
313010-01	C	6'7"	16	13	SJT	5-15P	C13 RA+	√
313011-01	C	7'6"	16	13	SJT	5-15P	C13 RA+	√
313014-01	C	9'10"	16	13	SJT	5-15P	C13 RA+	√
315005-01	H	6'7"	18	10	SJT	ROJ	C13	√
315008-01	H	9'10"	18	10	SJT	ROJ	C13	√
315086-01□	H	9'10"	18	10	SJT	ROJ	C13	√
316005-01□	H	6'7"	18	10	SJT	ROJ	C13 RA+	√
316009-01	H	6'7"	16	13	SJT	ROJ	C13 RA+	√
317003-01□	H	4'11"	18	10	SVT	C14	ROJ	√
317005-01	H	3'3"	18	10	SJT	C14	ROJ	√
318002-01	H	3'3"	18	10	SVT	C14	C13	√
318004-01	H	1'8"	18	10	SJT	C14	C13	√
318005-01	H	3'3"	18	10	SJT	C14	C13	√
318007-01	H	3'3"	16	13	SJT	C14	C13	√
331010-01□	I	9'10"	14	15	SJT	C20	C19	√
338010-01	J	7'6"	16	13	SJT	5-15P	C15	√
350049-LD01	K	6'0"	18	10	SVT	5-15P	C5	√
350050-LD01	K	10'0"	18	10	SVT	5-15P	C5	√

KEY:
□ - Voltage Rating 250VAC
• - Temperature Rating 105° C
* - Polarized
+ - RA= Right Angle
◆ - Split 2" and stripped 5/8"

Color Designation by Suffix (-xx)
01 - Black
03 - Brown
06 - Gray
08 - White
12 - Ivory
Other Colors Available

NOTES:
Click on part number for PDF download
All North American Cords are 125VAC / 60°C unless marked otherwise (adjacent to part number)
Cords marked ROJ: outer jacket is removed 2" and stripped 5/8"
Cords marked Split: outer jacket is split 1 1/2" and stripped 5/8"
North American color code: Black, White, Green
CEE Color Code: Brown, Blue, Green/Yellow Stripe
Custom Designs Available

7610 Jenther Drive * Mentor * Ohio * 44060-4872 * USA * Fax: 1-440-951-7252 * Phone: 1-440-951-3300

Follow @Qualtekelectron