



SMA Connectors MIL-C-39012 — For Semi-Rigid Cable (Continued)


MIL-C-39012/81



Outline 1



Outline 2



Outline 3

Military Part No.	AMP Part No.	M/A-COM [®] Part No. (Ref. Only)	Outline	Category	RG/U Cable
B3001	1050923-1	2002-8001-90	1	B	405
B3002	1050924-1	2002-8002-90	1	B	402
B3003	1084643-1	2002-8003-92	2	B	405
B3003	1050932-1 ¹	2002-8203-92	3	B	405
B3004	1050925-1	2002-8004-92	2	B	402
B3004	1050933-1 ¹	2002-8204-92	3	B	402

¹ OSCC solderless compression crimp version.



² -92 indicates passivated stainless steel finish.

-90 indicates gold plated finish.


See page 7003 for description of categories and pages 7059-7064 for tooling.

Military Part No.	AMP Part No.	M/A-COM [®] Part No. (Ref. Only)	Outline	Category	RG/U Cable
-3005	1050926-1	2002-8005-90	1	E	405
-3006	1050928-1	2002-8006-90	1	E	402
-3007	1050929-1	2002-8007-92	2	E	405
-3008	1050931-1	2002-8008-92	2	E	402
-3207	1050934-1 ¹	2002-8207-92	3	F	405
-3208	1050935-1 ¹	2002-8208-92	3	F	402


MIL-C-39012/82



Outline 4



Outline 5



Outline 6

Military Part No.	AMP Part No.	M/A-COM [®] Part No. (Ref. Only)	Outline	Category	RG/U Cable
B3001	1051087-1	2006-8001-90	4	B	405
B3002	1051088-1	2006-8002-90	4	B	402
B3003	1051089-1	2006-8003-92	6	B	405
B3003	1051095-1 ¹	2006-8203-92	5	B	405
B3004	1051090-1	2006-8004-92	6	B	402
B3004	1051096-1 ¹	2006-8204-92	5	B	402

¹ OSCC solderless compression crimp version.

² -92 indicates passivated stainless steel finish.

-90 indicates gold plated finish.

See page 7003 for description of categories and pages 7059-7064 for tooling.

Military Part No.	AMP Part No.	M/A-COM [®] Part No. (Ref. Only)	Outline	Category	RG/U Cable
-3005	1051091-1	2006-8005-90	4	E	405
-3006	1051092-1	2006-8006-90	4	E	402
-3007	1051093-1	2006-8007-92	6	E	405
-3008	1051094-1	2006-8008-92	6	E	402
-3207	1051097-1 ¹	2006-8207-92	5	F	405
-3208	1051098-1 ¹	2006-8208-92	5	F	402

RF Connectors