

PSB 4/7/6 - Test plug strip

0303299

<https://www.phoenixcontact.com/us/products/0303299>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, number of positions: 1, color: silver-colored

Your advantages

- Test sockets PSB ... are used for a reliable test pick-off
- All test sockets are screwed into the bridge shaft
- All test sockets are screwed into the bridge shaft

Commercial data

Item number	0303299
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918000417
Weight per piece (including packing)	2.25 g
Weight per piece (excluding packing)	2.17 g
Customs tariff number	85366990
Country of origin	PL

PSB 4/7/6 - Test plug strip

0303299

<https://www.phoenixcontact.com/us/products/0303299>



Technical data


Product properties

Product type	Test socket
Number of positions	1

Connection data

Connection method	Plug-in connection
-------------------	--------------------

Dimensions

Dimensional drawing	
Width	6 mm
Height	6 mm
Pin diameter	4.1 mm

Material specifications

Color	silver-colored
Contact material	Silver-plated brass

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 80 °C


PSB 4/7/6 - Test plug strip

0303299

<https://www.phoenixcontact.com/us/products/0303299>



Drawings



PSB 4/7/6 - Test plug strip

0303299

<https://www.phoenixcontact.com/us/products/0303299>



Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

ETIM

ETIM 9.0	EC002555
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PSB 4/7/6 - Test plug strip



0303299
<https://www.phoenixcontact.com/us/products/0303299>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com