


Contact removal tool - VC-EW 1,6 - 1884869

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact removal tool, for turned and rolled CK- 1.6-... contacts

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 170080
GTIN	4017918170080
Weight per Piece (excluding packing)	28.200 g
Custom tariff number	82055980
Country of origin	Germany

Technical data

General

Note	for contact inserts HC-BB.../ HC-Q05.../ HC-COM8.../ HC-A 10-E...C / HC-A 16-E...C / HC-K 8/24-E...C / HC-M-06.../ HC-M-08.../HC-M-20...
	for contact inserts HC-BB.../ HC-Q05.../ HC-COM8.../ HC-A 10-E...C / HC-A 16-E...C / HC-K 8/24-E...C / HC-M-06.../ HC-M-08.../HC-M-20...
Assembly instructions	The sleeve side of the tool is located beneath the blue cap of the unlocking tool.
Connection	For the removal of turned or rolled CK 1,6...R... or CK1,6...D... series contacts, the VC-EW 1,6 tool (Item No. 1884869) is required. For turned and rolled CK 1,6...ST... pin contacts and turned CK 1,6 ED...BU... socket contacts, the sleeve side of the tool is used. For rolled CK 1,6 ER-BU... socket contacts, the needle side of the tool must be used. To release the contacts, the tool is inserted from the front of the contact inserts in order to open the release mechanism. By pulling the wire, the appropriate contact can then be pulled out of the crimp chamber.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Contact removal tool - VC-EW 1,6 - 1884869

Technical data

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 11.0	21049090
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	27379200
eCl@ss 7.0	27379217
eCl@ss 9.0	27379217

ETIM

ETIM 2.0	EC000384
ETIM 3.0	EC000384
ETIM 4.0	EC002032
ETIM 6.0	EC002032
ETIM 7.0	EC002032

UNSPSC

UNSPSC 6.01	27112301
UNSPSC 7.0901	27112301
UNSPSC 11	27112301
UNSPSC 12.01	27112301
UNSPSC 13.2	27113201
UNSPSC 19.0	27113201

Approvals

Approvals

Approvals

EAC




Contact removal tool - VC-EW 1,6 - 1884869

Approvals

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------