



# JST Shop

[\(index\)](#)[Business calendar](#)[Shipping fee](#)

## Products name:BHF-001T-0.8BS

Series Name: NH CONNECTOR  
bulk contact type

NH contact



(C) 2016 J.S.T Mfg Co.,Ltd

[Add another product](#)[Previous](#)

Quantity	
----------	--

Quantity
----------

[Calculate](#)

Unit price :

Amount :

[Add to shopping cart](#)[Add to inquiry cart](#)

Shopping Cart Sub Total(Item0): 0.00 USD

Inquiry Cart Sub Total(Item0): 0.00 USD

## Products basic information

<b>Product code</b>	38526200
<b>Products name</b>	BHF-001T-0.8BS
<b>Pitch</b>	2.5mm
<b>Number of poles</b>	-----
<b>Color</b>	-----
<b>packing type</b>	Package
<b>plating</b>	-----
<b>Drawing</b>	-----
<b>Other information 1</b>	-----
<b>Other information 2</b>	-----
<b>Other information 3</b>	-----

## Pattern

-----	-----
-------	-------

## Prices

(Number of products)

(Number of products)

10	0.1565 USD	300	0.0374 USD
20	0.1224 USD	400	0.0306 USD
30	0.0952 USD	500	0.0272 USD
50	0.0748 USD	5000	0.0204 USD
100	0.0578 USD	80000	0.0197 USD
200	0.0476 USD		

## Series information

<b>Series Name</b>	NH CONNECTOR		
<b>Category</b>	Wire to Board Crimp style Connectors		
<b>Product type</b>	Crimp style, With locking device Disconnectable type		
<b>Manual</b>	This is a 2.5 mm pitch connector for connecting PC boards and wires, and consists of a contact, housing and header. There are three types of Header: top, side and bottom entry types, which allow wires to be drawn up, down, or parallel to the PC board by combining them.		
<b>Pitch</b>	2.5mm		
<b>Rated current</b>	3A (AWG#22)		
<b>Rated voltage</b>	250V		
<b>Mounting direction</b>	Top entry, Side entry, Bottom entry		
<b>Features</b>	-----		
<b>Catalog</b>	 1:eNH (pdf_show?kbn=1&key=eNH.pdf)	 2:eSM (pdf_show?kbn=1&key=eSM.pdf)	
<b>user's manual</b>	 CHM-1-2051		

## Member Information

Member Registration

Password reset

Account details

Address book

## Shipping method

Shipping fee

About correspondence of defective goods

About returned goods of damaged or misdelivery

**Payment etc.**

Payment method

Publication of the specifications

About issue the environment data documents

Contact us

© 2008-2024 J.S.T.MFG. CO.,LTD. All rights reserved.