


2956819

<https://www.phoenixcontact.com/us/products/2956819>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronics housing base element with snap-on foot for mounting on standard DIN rail, 35 mm wide

Commercial data

Item number	2956819
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AC11
Product key	ACHCCF
GTIN	4017918085957
Weight per piece (including packing)	84 g
Weight per piece (excluding packing)	77.3 g
Customs tariff number	85369010
Country of origin	DE

2956819


<https://www.phoenixcontact.com/us/products/2956819>

Technical data

Product properties

Product type	Enclosure bottom part
Housing type	Component housing
Housing series	UEG
Product family	UEG-EU
Type	Housing base element, side panels necessary to complete the module
Type	Base element

Dimensions

Dimensional drawing	
Width	35 mm
Depth	172 mm
Length	172 mm

Material specifications

Color (Housing)	green (RAL 6021)
Housing material	Polyamide fiber reinforced

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 105 °C

UEG-EU-BE - Electronics housing


2956819

<https://www.phoenixcontact.com/us/products/2956819>




Drawings

Dimensional drawing



Dimensional drawing



Maximum height of the components on the PCB, for 1 PCB


UEG-EU-BE - Electronics housing

2956819

<https://www.phoenixcontact.com/us/products/2956819>




Dimensional drawing




Maximum height of the components on the PCB with 2 PCBs

Dimensional drawing



Exploded view



UEG-EU-BE - Electronics housing

2956819

<https://www.phoenixcontact.com/us/products/2956819>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2956819>



UL Recognized

Approval ID: E240868

2956819

<https://www.phoenixcontact.com/us/products/2956819>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com