Part Number : 2317502042
Product Description : CP-3.3 Female-to-CP-3.3 Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin (Sn) Plating, 4 Circuits, Black
Series Number : 231750
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2317502042_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	231750
Description	CP-3.3 Female-to-CP-3.3 Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin (Sn) Plating, 4 Circuits, Black
Application	Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	CP-3.3-to-CP-3.3
Product Name	CP-3.3
Type	Discrete Wire Assembly
UPC	198930860174

Electrical

Current - Maximum per Contact	4.5A
Voltage - Maximum	500V AC (RMS)/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	7.275/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.30mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
CP-3.3 Plug Housing, 3.30mm Pitch, Single Row, Polarized, Positive Inertia Lock, 6 Circuits, Black	5046940601

Use with Part(s)

Description	Part Number
CP-3.3 Terminal Position Assurance (TPA) Retainers	504695

Downloaded from Arrow.com.