

SmartRack 3U Fan Panel - 3 208-240V high-performance fans; 315 CFM; C14 inlet

MODEL NUMBER: SRXFAN3U



Highlights

- 3U rack mount fan panel
- Ideal for increasing the ventilation of SmartRacks
- Features (3) 208-240V fans mounted in a 3U rack panel
- Required mounting hardware included
- Cold rolled steel with black finish

Package Includes

- Fan unit with C14 power inlet and required mounting hardware. User-supplied cord required.

Description

This SRXFAN3U SmartRack® panel-mount Triple Fan Accessory (for use with SmartRacks) is ideal for increasing the ventilation of SmartRacks, enclosures and server cabinets. The unit features three four-inch 208V-240V fans mounted in a 3U panel and includes mounting hardware.

Features

- SRXFAN3U SmartRack Panel-mount Triple Fan Accessory (for use with SmartRacks) is ideal for increasing the ventilation of SmartRacks, enclosures and server cabinets
- Unit features (3) 4-in.-208-240V fans mounted in a 3U panel
- Includes mounting hardware

Specifications

OVERVIEW	
UPC Code	037332144843
Accessory Type	Cooling Accessories
Accessory Class	Rack Accessories
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 230V AC; 240V AC
Nominal Input Voltage Description	208-240V AC 50/60 Hz
Voltage Compatibility (VAC)	208; 220; 230; 240
Input Frequency	50/60 Hz
OUTPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

Frequency Compatibility	50 / 60 Hz
COOLING	
Cooling Type	Passive
PHYSICAL	
Rack Height	3U
Shipping Dimensions (hwd / in.)	7.60 x 4.00 x 20.60
Shipping Dimensions (hwd / cm)	19.30 x 10.16 x 52.32
Shipping Weight (lbs.)	5.80
Shipping Weight (kg)	2.63
Unit Dimensions (hwd / in.)	5.220 x 18.870 x 1.500
Unit Dimensions (hwd / cm)	13.26 x 47.9 x 3.81
FEATURES & SPECIFICATIONS	
Sound Level (Noise)	45dB
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.