

Programmable Relay I/O Card

MODEL NUMBER: **RELAYIOCARD**



Highlights

- Programmable, internal contact closure management accessory card
- Six configurable relay output contacts
- Configurable input signal contact

Package Includes

- RELAYIOCARD
- Configuration cable
- Faceplates
- Owner's Manual

Description

Tripp Lite's RELAYIOCARD allows users to communicate UPS status and events via six configurable contact closure outputs. Installs in select expansion slot-equipped SmartOnline and select SmartPro UPS systems*. Enables monitoring of UPS conditions and events. Provides input signal relay contact to perform remote UPS system shutdown or battery tests.

*NOTE: SmartPro UPS systems including SMART1050SLT, SMART1500SLT, SMART2200RMXL2U, SMX1050SLT, SMART3000SLT, SMART2200SLT, SMART2200NAFTA, SMART2600RM2U, SMART3000RM2U, SMART1500CRMXL, SMART750XL, SMX2200XLRT2U, and SMX3000XLRT2UA. Supported SmartPro systems must run UPS protocol 3008 or above. Works with most Tripp Lite Smart Online series models except the following; SU3000RTXL2U, SUINT3000RTXL2U, SUINT1000LCD2U, SUINT1500LCD2U, SUINT2200LCD2U, SUINT3000LCD2U, and SU3000LCD2UHV models.

Features

- Makes select Tripp Lite SmartPro or SmartOnline UPS capable of providing contact closure output communications
- 6 relay output contacts are configurable for normal open or normal close signaling of UPS conditions
- Configurable UPS conditions and events for each output relay contact
- Configurable input signal relay contact to shutdown UPS or test battery

Specifications

OVERVIEW	
UPC Code	037332146410



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
Output Connector Type	Six configurable output relays; Screw-down terminal interface support 16-22 AWG wire sizes
PHYSICAL	
Shipping Dimensions (hwd / cm)	15.24 x 4.44 x 15.75
Shipping Dimensions (hwd / in.)	6.00 x 1.75 x 6.20
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
COMMUNICATIONS	
Communications Interface	Contact closure
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>