


PRODUCT NUMBER
SEE TABLE, SHEET 2







CONFIDENTIAL

www.fciconnect.com			surface - ASME Y14.5		tolerance std - ASME Y14.5		projection	MM
TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	T.HOUTZ	2005-11-01	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 4:1
Eng	C. H. TAN	2006-06-05			0.XX	±0.10		
Chr	C. H. TAN	2007-06-04	0° ±2°		0.XXX	±0.050	ECN ***	
Appr	JOEY NG	2007-06-04	Product family -				Spec ref -	

rev	ecn no	dr	date
A	S06-0199	CH	2006-06-05
B	S07-0055	LS	2007-06-04
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

title	AirMax COVER R/A HDR & RECPT - 5pr, 2mm	dwg no	10062848 Rev. B
catalog no -		CUSTOMER	sheet 1 of 2

Copyright FCI.

REV F - 2006-04-17


PDM: Rev:B

STATUS:Released

Printed: Dec 01, 2010


Downloaded from Arrow.com.

PART NUMBER (NOTE 3)	CONNECTOR GENDER	NUMBER OF IMLAS	DIM A	DIM C
10062848-001LF	R/A HEADER	6	11.90	18.00
10062848-002LF	R/A HEADER	8	15.90	18.00
10062848-003LF	R/A HEADER	10	19.90	18.00
10062848-004LF	R/A RECEPT.	6	11.90	23.45
10062848-005LF	R/A RECEPT.	8	15.90	23.45
10062848-006LF	R/A RECEPT.	10	19.90	23.45



10062848-003LF SHOWN

SCALE 4:1



10062848-006LF SHOWN

SCALE 4:1

NOTES:

1. MATERIAL: THERMOPLASTIC RESIN
   COLOR : BLACK,
   UL94V-0 COMPLIANT,
   MAXIMUM OPERATING TEMPERATURE
   IS 105°C.
2. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
4. PACKAGING MEETS GS-14-920 LEAD FREE LABELLING SPECIFICATION.

Copyright FCI.

CONFIDENTIAL

title: AirMax COVER R/A HDR & RECPT - 5pr, 2mm	dwg no: 10062848	Rev. B	
catalog no: -	CUSTOMER	sheet 2 of 2	

REV F - 2006-04-17

PDM: Rev:B

STATUS: Released 8 Printed: Dec 01, 2010

Downloaded from Arrow.com.