



Competitors/Distributors part #

Product # or Keyword



North America

NA

AS

EU

Industries Served

Products

Resources

Support

Company

Contact

M12 Connector, 3-Position Female Right Angle, 18-22AWG

Home ▶ Products ▶ Field Wireable Connectors ▶ M12 Connector, 3-Position Female Right Angle, 18-22AWG



Description

M12 Connector, 3-Position Female Right Angle, 18-22AWG

Model #: BU-12ZU22-PG9
Category: Field Wireable Connectors
Data Files:
[BU-12ZU22-PG9-New.jpg](#)

Product Details

Connection Configuration

Female

Wire Gauge (AWG)

18-22

Shell Size

M12

Coding

A (Micro DC)

Number of Positions

3

Voltage

250 V AC/DC

Body Material

Unshielded Nylon 66

Cable Diameter

6mm-8mm

Degree Of Protection

IP67

Standards / Regulations

IEC 61076-2-101

Orientation

Right Angle

RoHS Compliant

3 Compliant

Inventory & Distributors

Mueller Inventory: 596

Distributor Inventory: 4

[Check Distributor Inventory and Pricing](#)

— ASK A QUESTION

about BU-12ZU22-PG9

Full Name

Company

Email address

Phone number

Message

SEND

Connect with us on social media



Sign up for our newsletter

Email Address

Sign Up

Products & Services

[View all products](#)

[Product Search](#)

[Accessories](#)

[Cable Lugs](#)

[Clips](#)

[Connectors](#)

[Grounding Cables](#)

[Instrumentation Cables](#)

[Kits](#)

[Test Leads](#)

[Temporary Protective Grounds](#)

[Wire & Cable](#)

Industry Solutions

[Aerospace](#)

[Battery](#)

[Instrumentation](#)

[Medical](#)

[Military & Defense](#)

[Paint Grounding](#)

[Substation Maintenance](#)

[Test and Measurement](#)

[Underground Sensing](#)

Quick Links

[About Us](#)

[Full Catalog](#)

[Free Guides](#)

[FAQs](#)

[Media & Downloads](#)

[Blog](#)

[Contact Us](#)

[Policies](#)



Mueller Electric USA

2850 Gilchrist Rd. Building 5A, Akron, OH 44305

sales@muellerelectric.com

Toll Free: 1(800) 955 - 2629

Phone: (330) 780 - 2525

Fax: 330-780-2524

Mueller Electric Europe

Unit 9, Castle Park Industrial Estate, Queens Drive, Nottingham NG2 1AH, United Kingdom

EuropeSales@muellerelectric.com

Tel: +44 (0) 1159 933300

Fax: +44 (0) 1159 933301


[LEARN MORE - EUROPE](#)

Mueller Electric China

6th Floor, Bldg-3, No.1295 Xin Jinqiao Rd, Shanghai, China
P.C.:201206

TEL: +86 185 1626 6177

[LEARN MORE - ASIA](#)



IEC 1010
COMPLIANT



DSCC

