

Female test connector - PSBJ 6-T WH



3070324

<https://www.phoenixcontact.com/us/products/3070324>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Female test connector, color: white

Commercial Data

Item number	3070324
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B01
Product Key	BE1Z3X
Catalog Page	Page 567 (C-1-2017)
GTIN	4046356753777
Weight per Piece (including packing)	5.67 g
Weight per Piece (excluding packing)	4 g
Customs tariff number	85366990
Country of origin	PL

Female test connector - PSBJ 6-T WH



3070324

<https://www.phoenixcontact.com/us/products/3070324>

Technical Data


Product properties

Product type	Test plug terminal block
Number of positions	1

Connection data

Test socket torque	M3
--------------------	----

Dimensions

Dimensional drawing	
Width	6 mm
Height	15 mm
Length	6 mm
Pin diameter	4 mm
Screw thread	M3

Material specifications

Color	white
Material	Brass
Insulating material	PA
Contact material	PE-LD, silver-plated brass

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Screw thread	M3
--------------	----


Female test connector - PSBJ 6-T WH

3070324

<https://www.phoenixcontact.com/us/products/3070324>



Drawings



Female test connector - PSBJ 6-T WH



3070324

<https://www.phoenixcontact.com/us/products/3070324>

Classifications

ECLASS

ECLASS-9.0	27440313
------------	----------

ETIM

ETIM 7.0	EC002255
----------	----------

Female test connector - PSBJ 6-T WH



3070324

<https://www.phoenixcontact.com/us/products/3070324>

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Female test connector - PSBJ 6-T WH



3070324

<https://www.phoenixcontact.com/us/products/3070324>

Accessories

Screwdriver

Screwdriver - SZF 1-0,6X3,5 - 1204517

<https://www.phoenixcontact.com/us/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Screwdriver

Screwdriver - SF-SL 0,6X3,5-100 S-VDE - 1212587

<https://www.phoenixcontact.com/us/products/1212587>



Actuation tool, for ST terminal blocks, VDE insulated, with slimmer insulation integrated in the blade, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com