

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002091615

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 42477, Female, with Tin (Sn) Plated Contact, High Current/Low Engagement Force, 14-18 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-42477-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	42477
Application	Power, Wire-to-Wire
Comments	High Current/Low Force
Crimp Quality Equipment	Yes
Overview	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
UPC	800753684393
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.417/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	14, 16, 18
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	17.0A
Voltage - Maximum	250V AC (RMS)
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	42477-0005
Reference - Drawing Numbers	
Product Specification	PS-42477-001
Sales Drawing	SD-42477-XXXX



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42477 Series

Use With

Standard .093 Plug or Receptacle Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool for Standard .093" Pin and Socket Terminals	11020003
Extraction Tool for Standard .093" Pin and Socket Terminals	11030006
PremiumGrade Hand Crimp Tool for Standard .093"	638117100

Pin and Socket
Terminals 14-18
AWG and 24-30
AWG and Claspcon
Crimp Terminal
Socket 24-30 AWG
Extractor Tool 638240200
for .093 and
HCS-125 Product
Series
FineAdjust Applicator639024600
for .093" Pin and
Socket Terminals
FineAdjust Applicator639024700
for 2.63mm Pin and
Socket Terminal
T2 Terminator for 639124600
2.00mm Pitch Wire-
to-Board Crimp
Terminal
T2 Terminator Die 639124700

This document was generated on 02/24/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION