



**Part Number :** [1300840136](#)

**Product Description :** Woodhead POW-R-MITE Heavy Duty Cable Reel with Retraction Weight of 4lbs., 6/3 Type W, 9.14m (30.0') Cord Length with Flying Leads

**Series Number :** 130084

**Status :** Active

**Product Category :** Electrical Reels

**Engineering Part Number :** 92536N



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Electrical Reels
Series	130084
Description	Woodhead POW-R-MITE Heavy Duty Cable Reel with Retraction Weight of 4lbs., 6/3 Type W, 9.14m (30.0') Cord Length with Flying Leads
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 3
NEMA Configuration	N/A
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678827479

### Agency

CSA	LR29921
-----	---------

### Electrical

Current - Maximum per Contact	45.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

### Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock

Cord Length	9.14m (30.0')
Cord Type	6/3 Type W
Depth	0.48m (19.00")
Drum Lock	Ratchet
Duty	Heavy
Guide Arm	4 - Postion
Height	0.52m (20.50")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	Rigid
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Width	423.42mm (16.670")
Wire Size (AWG)	6

---

This document was generated on May 24, 2026